


[See all 3 Products in Family](#)

OD 0.04 - 2.0, 50.8 x 25.4mm Stepped ND Filter



Stock **#64-383** **7 In Stock**

- 1 + £189^{.60}

ADD TO CART

Volume Pricing

Qty 1-10	£189.60 each
Qty 11-25	£171.20 each
Qty 26-49	£162.40 each
Need More?	Request Quote

! Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Neutral Density Filter **Type:**

Physical & Mechanical Properties

25.4 x 50.8 **Dimensions (mm):**

2.0 **Length (inches):**

50.80	Length (mm):
0.062	Thickness (inches):
1.0	Width (inches):
25.40	Width (mm):

Optical Properties

0.04 - 2.0	Optical Density OD (Average):
Float Glass	Substrate: <input type="checkbox"/>
Stepped Variable	Coating:
400 - 700	Blocking Wavelength Range (nm):


Regulatory Compliance

View	Certificate of Conformance:
----------------------	------------------------------------

Product Details

- 11 Discrete Density Steps
 - Design Wavelength of 400 - 700nm
 - Density Neutrality of $\pm 5\%$
- Density and transmission vary in eleven equal steps across the surface length. The steps are abrupt changes and no light escapes between them. Spectrally flat neutral density coating. Ideal for applications requiring variable densities and known density values.

Technical Information



Compatible Mounts