

OD 0.9 NIR, 25mm Dia. Non-Reflective ND Filter



Non-Reflective Neutral Density (ND) Filters

Stock **#63-409** 3-4 DAYS



1



£119.85

ADD TO CART

Qty 1-10

£119.85

Qty 11+

£107.69

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
25.00 ±0.10

Optical Density OD (Average):
0.9

Substrate: ☐
[B270](#)

Coating: Non-Reflective ND
Reflection (%): ≤1.5
Surface Quality: 60-40
Thickness (mm): 1.50
Thickness Tolerance (mm): ±0.1
Transmission (%): 12.50
Transmission Tolerance (%): ±1
Type: Neutral Density Filter
Parallelism (arcmin): <5
Clear Aperture (%): 90.00
Surface Accuracy: 2λ
Wavelength Range (nm): 700 - 1200

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View