

SCHOTT OG-515, 25.4mm Dia., 3mm Thick, Colored Glass Longpass Filter

See More by [SCHOTT Optical Components](#)



Stock **#45-069** ☐ In Stock

-

1

+

£32.94

ADD TO CART

Qty 1-10
£32.94
Qty 11+
£32.30
Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
25.40

Cut-Off Position λ_c (nm):
515±6

Cut-On Wavelength (nm): 515.00
Density (g/cm³): 2.56
Glass/Filter Number: SCHOTT OG515
Coating: Uncoated
Color: Yellow
Passband Limit 1 λ_{p1} (nm): 580.00
Spectral Transmittance t_p (%): 93.00
Stopband Limit λ_s(nm): 440.00
Surface Quality: 80-50
Transformation Temperature (°C): 509.00
Thickness (mm): 3.00 ±0.2
Type: Longpass Filter
Wavelength: VIS
Dimensional Tolerance (mm): ±0.38
Reflection Factor P_d: 0.92
Bevel: Protective as needed

Regulatory Compliance

RoHS 2015: Exempt
Reach 224: Compliant
Certificate of Conformance: View