

[See all 16 Products in Family](#)

Olympus Low Auto Fluorescence Immersion Oil

See More by [Olympus](#)



#86-834



Stock **#86-834** **20+ In Stock**

− 1 + £70⁴⁰

ADD TO CART

| Volume Pricing | |
|----------------|-------------------------------|
| Qty 1+ | £70.40 each |
| Need More? | Request Quote |

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Olympus **Manufacturer:**

Optical Properties

1.518 **Index of Refraction (n_d):**

Environmental & Durability Factors

Operating Temperature (°C):
23

Regulatory Compliance

Certificate of Conformance:
[View](#)

Product Details

- High Numerical Aperture (NA) up to 1.45
- Chromatic Aberration Correction from 400 - 1000nm
- Uniform Image Flatness over Large FOVs

Olympus X-Line Extended Apochromat Infinity Corrected Objectives (also referred to as the UPLXAPO series) are Olympus' next generation high performance objectives that simultaneously feature high numerical aperture (NA), broadband chromatic aberration correction, and excellent image flatness. The high numerical aperture (NA) allows for excellent light collection efficiency to better capture faint signals, enabling a shorter exposure time and higher contrast. The broad chromatic aberration correction compensates for the wavelength-dependent spatial shift of colors to achieve excellent color reproduction. These objectives also achieve high image flatness from the center to the edges of images over large fields of view (FOV), making them ideal for image stitching and quantitative image analysis. Olympus X-Line Extended Apochromat Infinity Corrected Objectives are used in demanding life science and clinical applications including pathology, fluorescence microscopy, multicolor or widefield fluorescence imaging, confocal or super resolution microscopy, and whole slide imaging.

Technical Information

| | Stock # | A | B | C | D | E | F | G | WD |
|--|-------------------------|-------|------|------|------|------|------|-----|-------|
| Olympus UPLXAPO 4X Objective | #14-905 | 31.89 | - | - | 15.4 | 15.4 | 28 | 4.7 | 13.0 |
| Olympus UPLXAPO 10X Objective | #14-906 | 41.78 | 3.7 | 4.28 | 9.6 | 19.4 | 28 | 4.6 | 3.1 |
| Olympus UPLXAPO 20X Objective | #14-907 | 44.28 | 3.39 | 2.88 | 10.2 | 18.6 | 28 | 4.8 | 0.61 |
| Olympus UPLXAPO 40X Objective | #14-908 | 44.71 | 4.21 | 2.11 | 7.5 | 20.3 | 31.5 | 4.9 | 0.18 |
| Olympus UPLXAPO 60X Oil Immersion Objective | #14-909 | 44.74 | 2.1 | 2.84 | 10 | 19.3 | 31.5 | 4.9 | 0.15 |
| Olympus UPLXAPO 100X Oil Immersion Objective | #14-910 | 44.76 | 2.1 | 3.06 | 7.5 | 19.1 | 30.5 | 4.8 | 0.135 |

