

Olympus UPLXAPO 10X Objective

See More by [Olympus](#)



Olympus UPLXAPO 10X Objective, #14-906

Stock **#14-906** 3-4 DAYS



1



£2,396.15

ADD TO CART

Qty 1+

£2,396.15

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Compatible Cover Glass Thickness (mm):
0.17

Field of View (mm):
2.65

Focal Length FL (mm):
18.00

Model Number:
UPLXAPO10X

Length excluding Threads (mm): 41.96
Magnification: 10X
Maximum Diameter (mm): 28
Numerical Aperture NA: 0.40
Mounting Threads: RMS / 20.32mm x 36 TPI
Compatible Tube Lens Focal Length (mm): Focal Length: 180mm
Type: Microscope Objective
Resolving Power (µm): 0.84
Depth of Field (µm): 1.72
Working Distance (mm): 3.1
Weight (g): 141
Wavelength Range (nm): 300 - 1000
Style: Infinity Corrected
Manufacturer: Olympus
Field Number (mm): 26.5
Parfocal Length (mm): 45.06
Immersion Liquid: N/A

Regulatory Compliance

Certificate of Conformance: View
--