

## Pixelink M-Series M2M-CYL Microscopy Monochrome Camera



Stock #17-818 3-4 DAYS

-

1

+

£1,100.75

ADD TO CART

|           |
|-----------|
| Qty 1+    |
| £1,100.75 |

|                               |
|-------------------------------|
| Volume Pricing                |
| <a href="#">Request Quote</a> |

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

**Video Output:**  
USB 3.0

**Type:**  
Monochrome Microscopy Camera

**Manufacturer:**  
Pixelink

**Mounting Threads:**  
No Mounting Threads/Tripod Adapter

**Image Buffer:**  
Not Specified

|                                                                |
|----------------------------------------------------------------|
| <b>Camera Family:</b><br>M-Series                              |
| <b>Model Number:</b><br>M2M-CYL                                |
| <b>Imaging Sensor:</b><br>CMOSIS CMV2000                       |
| <b>Type of Sensor:</b><br>Progressive Scan CMOS                |
| <b>Type of Shutter:</b><br>Global                              |
| <b>Camera Sensor Format:</b><br>2/3"                           |
| <b>Resolution (MegaPixels):</b><br>2.20                        |
| <b>Pixels (H x V):</b><br>2,048 x 1,088                        |
| <b>Pixel Size, H x V (µm):</b><br>5.5 x 5.5                    |
| <b>Sensing Area, H x V (mm):</b><br>11.3 x 6.0                 |
| <b>Frame Rate (fps):</b><br>169.80                             |
| <b>Pixel Depth:</b><br>8/10 bit                                |
| <b>Exposure Time:</b><br>Not Specified                         |
| <b>Connector:</b><br>USB 3.0, Micro-B                          |
| <b>Power Supply:</b><br>Power over USB                         |
| <b>Power Consumption (W):</b><br>Not Specified                 |
| <b>GPIOs:</b><br>None                                          |
| <b>Synchronization:</b><br>Software Trigger                    |
| <b>Dimensions (mm):</b><br>85.68 x 54.01 (excludes lens mount) |
| <b>Weight (g):</b><br>218.5                                    |
| <b>Mount:</b><br>C-Mount                                       |
| <b>Housing:</b><br>Full                                        |
| <b>Interface Port Orientation:</b><br>Back Panel               |
| <b>Dynamic Range (dB):</b><br>60                               |
| <b>Operating Temperature (°C):</b><br>0 to +50                 |
| <b>Storage Temperature (°C):</b><br>-45 to +85                 |
| <b>GPIO Connector Type:</b><br>None                            |
| <b>Machine Vision Standard:</b><br>USB3 Vision                 |

## Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Reach 224:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |