

[See all 43 Products in Family](#)

Power Supply for 0.5-0.8mW HeNe Laser, 24 VDC, Bare Wire Leads



L28 Series with CDRH Delay HeNe Laser Power Supply

Stock **#11-383** **3 In Stock**

-

1

+

£280⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	£280.00 each
Need More?	Request Quote

i Prices shown are exclusive of VAT/local taxes

Product Downloads



General

OEM

Type:

Compatible Laser Models:

[1108](#), [1108P](#), [1107](#), [1107P](#)

L28 Series

Model Number:

Compatible Laser Stock Number:

[#62-714](#), [#62-715](#), [#62-716](#), [#62-717](#)

CDRH Delay (3-5 seconds)		Features:
Physical & Mechanical Properties		
4.00 x 1.50 x 1.00		Dimensions (inches):
Electrical		
5		Output Power (W):
0.95 (Max. Current Draw)		Input Current (A):
Hardware & Interface Connectivity		
1250		Output Voltage (V):
4		Output Current (mA):
High Voltage Alden Connector		Connector:
22-30 DC		Input Voltage (V):
Regulatory Compliance		
View		Certificate of Conformance:

Product Details

- Power Options from 0.5 - 22.5mW
- Improved Stability
- Ideal for Interferometry and Metrology Applications
- Random or Linear Polarization Options

Lumentum High Performance Helium-Neon Lasers feature a patented close-cathode design that provides improved thermal and power stability. They also utilize a patented field concentrator design that enables fast turn-on. These Lumentum HeNe lasers also feature precisely aligned cylindrical housings, with cylindrical laser heads and electrical interconnect systems used to simplify system integration. Lumentum High Performance Helium-Neon Lasers' rugged design is ideal for even the most demanding applications. They are exemplary for use within interferometry and metrology applications.

Note: Please exercise caution when using a user-provided power supply to not exceed the electrical specifications of the laser as this may cause damage and void the warranty. These HeNe lasers comply with 21CFR1040 and IEC 825-1:1993. Lumentum was previously known as JDSU.

Technical Information

Beam Expander Mounting Configurations

Click on an item below to be brought to that item's product page.

