

## Power Supply for 2mW HeNe Laser, AC, US Plug



Benchtop Power Supply, AC Input (Front)



Stock #11-389 **4 In Stock**

1 **£660<sup>00</sup>**

**ADD TO CART**

### Volume Pricing

Qty 1+	£660.00 each
Need More?	<a href="#">Request Quote</a>

Prices shown are exclusive of VAT/local taxes

### Product Downloads



### General

Benchtop

Type:

[1122, 1122P](#)

Compatible Laser Models:

SL92 Series

Model Number:

Compatible Laser Stock Number:  
[#62-720](#), [#62-721](#)

**Features:**  
Turn Key, CDRH Delay (3-5 seconds)

## Physical & Mechanical Properties

**Dimensions (inches):**  
9.00 x 5.50 x 2.38

## Electrical

**Output Power (W):**  
11.7

**Input Current (A):**  
0.55/0.32

## Hardware & Interface Connectivity

**Output Voltage (V):**  
1800

**Output Current (mA):**  
6.5

**Connector:**  
High Voltage Alden Connector

**Input Voltage (V):**  
100/110/220 (AC)

## Regulatory Compliance

**Certificate of Conformance:**  
[View](#)

## Product Details

- Power Options from 0.5 - 22.5mW
- Improved Stability
- Ideal for Interferometry and Metrology Applications
- Random or Linear Polarization Options

Lumentum High Performance Helium-Neon Lasers feature a patented close-cathode design that provides improved thermal and power stability. They also utilize a patented field concentrator design that enables fast turn-on. These Lumentum HeNe lasers also feature precisely aligned cylindrical housings, with cylindrical laser heads and electrical interconnect systems used to simplify system integration. Lumentum High Performance Helium-Neon Lasers' rugged design is ideal for even the most demanding applications. They are exemplary for use within interferometry and metrology applications.

**Note:** Please exercise caution when using a user-provided power supply to not exceed the electrical specifications of the laser as this may cause damage and void the warranty. These HeNe lasers comply with 21CFR1040 and IEC 825-1:1993. Lumentum was previously known as JDSU.

## Technical Information

### Beam Expander Mounting Configurations

Click on an item below to be brought to that item's product page.

□