

Hoya R66 (660nm), 12.5mm Dia., 2.5mm Thick, Colored Glass Longpass Filter

See More by [Hoya](#)



Stock **#66-045** 3-4 DAYS

⊖ 1 ⊕ **£27.20**

ADD TO CART

Qty 1-10
£27.20

Qty 11+
£23.80

Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
12.50

Cut-Off Position λ_c (nm):
660±6

Cut-On Wavelength (nm):
660.00 ±6

Density (g/cm³): 2.85
Glass/Filter Number: Hoya R66
Substrate: ☐ Colored Glass
Coating: Uncoated
Color: Red
Surface Quality: 80-50
Transformation Temperature (°C): 530
Thickness (mm): 2.50
Thickness Tolerance (mm): ±0.2
Type: Longpass Filter
Wavelength: VS
Dimensional Tolerance (mm): ±0.38
Reflection Factor P _d : 0.92
Bevel: Protective as needed
Δλ (nm): <35
TH (%): >85

Regulatory Compliance

RoHS 2015: Exempt
Reach 224: Compliant
Certificate of Conformance: View