


SCHOTT RG-630, 50.8mm Sq., 3mm Thick, Colored Glass Longpass Filter

See More by [SCHOTT Optical Components](#)



Stock **#32-765** CLEARANCE CONTACT US



1



£42.46

ADD TO CART

Qty 1+

£42.46

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Dimensions (mm):
50.8 x 50.8

Cut-Off Position λ_c (nm):
630±6

Cut-On Wavelength (nm):
630.00

Density (g/cm³):

2.65
Glass/Filter Number: SCHOTT RG630
Length (mm): 50.80
Coating: Uncoated
Color: Red
Passband Limit 1 λ_{p1} (nm): 710.00
Spectral Transmittance t_p (%): 94.00
Stopband Limit λ_s(nm): 540.00
Surface Quality: 80-50
Transformation Temperature (°C): 527.00
Thickness (mm): 3.00 ±0.2
Type: Longpass Filter
Wavelength: VIS
Width (mm): 50.80
Dimensional Tolerance (mm): ±0.38
Reflection Factor P_d: 0.92
Bevel: Protective as needed

Regulatory Compliance

RoHS 2015: Exempt
REACH 201: Compliant
Certificate of Conformance: View