

[All Products](#) / [Imaging Lenses](#) / [Fixed Focal Length Lenses](#) / [Rodagon Large Format Lenses](#)

[See all 15 Products in Family](#)

Rodagon 105mm FL - Video Lens



Lens + Modular Focus Tube + Basler Line Scan Camera

Stock **#14-703** ☐ In Stock

1

£739.50

ADD TO CART

Qty 1+

£739.50

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Note: This item requires accessories for use | [Learn More](#)

Get Product Downloads

Field of View @ Min Working Distance (mm):
54.0

Iris Option:
Variable

Length (mm):
41.00

Horizontal Field of View, 1/2" Sensor:
3.4°

Filter Thread: M40.5 x 0.50
Maximum Diameter (mm): 50.0
Maximum Image Circle (mm): 85.00
Note: Requires Leica Lens Adapter M39 x 1/26" #14-705 , Modular Focus Tube #14-707 , and a lens mount adapter (C-Mount , F-Mount , T-Mount , SLR , or M72)
Type: Fixed Focal Length Lens
Focal Length FL (mm): 105.00
Primary Magnification PMAG: 0.19X
Maximum Sensor Format: 85mm (Image Circle)
Working Distance (mm): 974 - ∞
Mount: Adapter Required
Aperture (f/#): f/5.6 - f/32
Lens Wavelength Range: VIS

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant