

TECHSPEC® 25mm ID Rotary Mount, M6



Rotary Mount, M6, #85-658

Stock #85-658 [CONTACT US](#)

⊖ 1 ⊕ £106⁴⁰

ADD TO CART

Volume Pricing

Qty 1+	£106.40 each
Need More?	Request Quote

! Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Rotary **Function:**
Circular/Cylindrical Tube **Type of Optics:**

Physical & Mechanical Properties

25.0 **Plate Inner Diameter (mm):**

Bolt Circle Diameter for 6mm Dia. Thru (mm):

38.0

Black Anodized Aluminum

Construction:

50 Dia.

Dimensions (mm):

21.00

Thickness (mm):

38.0

Bolt Circle Diameter for M3 Tapped (mm):

Threading & Mounting

M6 x 1.0

Compatible Post:

Regulatory Compliance

[Compliant](#)

RoHS 2015:

[View](#)

Certificate of Conformance:

[Compliant](#)

Reach 235:

Product Details

- Specialized Plates Designed to Hold and Position Optics
- Anodized Aluminum Construction with Stainless Steel Screws
- X-Y Micro Positioning Plate with RMS Mounting Thread

TECHSPEC® Cage System Adjustable Plates are used to integrate optical components into the TECHSPEC Cage System while providing rotary, tip-tilt, or linear adjustment. Rotary Mounts are available with M6 or 1/4-20 mounting threads and are designed to fit within the inner diameter of 25mm [cage system plates](#). The Kinematic Cage Mounting Plate is compatible with 30mm [cage system plates](#) and enables kinematic adjustment of cage system assemblies. The X-Y Micro Position Stage Plate also has 6mm rod holes, and features a 7mm clear aperture, X-Y micro-positioner, and an RMS threaded mount for precision mounting alignment.