

Schneider 80mm F-Mount Lens



Stock #34-235 3-4 DAYS



1



£1,330.25

ADD TO CART

Qty 1+

£1,330.25

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Field of View @ Min Working Distance (mm):
188 (35mm Sensor)

Iris Option:
Variable

Length (mm):
56.90

Filter Thread:
M43.0 x0.75

Maximum Diameter (mm):
49.0

Weight (g): 280.00
Maximum Rear Protrusion (mm): 4.5
Maximum Image Circle (mm): 60.00
Horizontal Field of View, 35mm Sensor: 30.1°
Note: Optimized Working Distance: 403 - 2062mm
Type: Fixed Focal Length Lens
Focal Length FL (mm): 80.00
Maximum Sensor Format: 60mm (Image Circle)
Working Distance (mm): 403 - ∞
Mount: F-Mount
Aperture (f/#): f/4.0 - 4/16
Distortion (%): <0.8
Coating: 400 - 1000 BBAR
Lens Wavelength Range: VIS-NIR Color Corrected

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant