

SCHOTT BG40, 12.5mm Dia., 1mm Thick, Colored Glass Bandpass Filter

See More by [SCHOTT Optical Components](#)



Stock **#16-367** 3-4 DAYS

[Additional Bandwidths](#)

⊖ 1 ⊕

£34.85

ADD TO CART

Qty 1-10
£34.85
Qty 11+
£31.45
Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
12.50

Center Wavelength CWL (nm):
514.00

Density (g/cm³): 2.74
Glass/Filter Number: SCHOTT BG40
Coating: Uncoated
Color: Blue-Green
Index of Refraction n _d : 1.53
Surface Quality: 60-40
Transformation Temperature (°C): 313
Thickness (mm): 1.00 ±0.1
Type: Bandpass Filter
Wavelength: UV-VIS
Bevel: Protective as needed

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant