



SCHOTT BG50, 12.5mm Dia., 2mm Thick, Colored Glass Bandpass Filter

See More by [SCHOTT Optical Components](#)



Stock **#16-380** 3-4 DAYS

[Additional Bandwidths](#)

-

1

+

£39.95

ADD TO CART

Qty 1-10
£39.95

Qty 11+
£34.85

Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
12.50

Center Wavelength CWL (nm):
500.00

Density (g/cm³): 2.61
Glass/Filter Number: SCHOTT BG50
Coating: Uncoated
Color: Blue-Green
Index of Refraction n_d: 1.53
Surface Quality: 60-40
Transformation Temperature (°C): 452
Thickness (mm): 2.00 ±0.2
Type: Bandpass Filter
Wavelength: UV-VIS
Bevel: Protective as needed

Regulatory Compliance

Certificate of Conformance: View
--