

SCHOTT BG50, 50mm Sq., 1mm Thick, Colored Glass Bandpass Filter

See More by [SCHOTT Optical Components](#)



Stock **#14-427** ☐ In Stock



1



£144.50

ADD TO CART

Qty 1-10

£144.50

Qty 11+

£129.20

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Dimensions (mm):

50.0 x 50.0

Center Wavelength CWL (nm):

500.00

Density (g/cm³): 2.61
Glass/Filter Number: SCHOTT BG50
Length (mm): 50.00
Coating: Uncoated
Color: Blue-Green
Index of Refraction n _d : 1.53
Surface Quality: 60-40
Transformation Temperature (°C): 452
Thickness (mm): 1.00 ±0.1
Type: Bandpass Filter
Wavelength: UV-VIS
Width (mm): 50.00
Bevel: Protective as needed

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View