

# Schott CV-LS RGBW Light Source

See More by [SCHOTT Optical Components](#)



Stock **#75-280** NEW **1 In Stock**

-

1

+

£1,388<sup>00</sup>

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1+         | £1,388.00 each                |
| Need More?     | <a href="#">Request Quote</a> |

 Prices shown are exclusive of VAT/local taxes

| Product Downloads |                             |
|-------------------|-----------------------------|
| General           |                             |
| >50,000           | Operating Lifetime (hours): |
| A20980/RGBW       | Model Number:               |
| Yes               | Intensity Control Option:   |
| LED Illuminator   | Type of Illumination:       |

|                                                                                                                                                                                                                                        |                             |
|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-----------------------------|
| SCHOTT                                                                                                                                                                                                                                 | Manufacturer:               |
| Constant                                                                                                                                                                                                                               | Illumination Mode:          |
| Physical & Mechanical Properties                                                                                                                                                                                                       |                             |
| 129W x 201D x 59.69H                                                                                                                                                                                                                   | Dimensions (mm):            |
| 0.816                                                                                                                                                                                                                                  | Weight (kg):                |
| Optical Properties                                                                                                                                                                                                                     |                             |
| Red, Green, Blue, or White                                                                                                                                                                                                             | Color:                      |
| Electrical                                                                                                                                                                                                                             |                             |
| Red: 130<br>Green: 250<br>Blue: 70<br>White: 400                                                                                                                                                                                       | Output Power (Lumens):      |
| Hardware & Interface Connectivity                                                                                                                                                                                                      |                             |
| 24 DC                                                                                                                                                                                                                                  | Input Voltage (V):          |
| Power Cord Required and Sold Separately.<br>USA: <a href="#">#75-296</a><br>Europe: <a href="#">#75-298</a><br>UK: <a href="#">#75-297</a><br>China: <a href="#">#75-296</a><br>Japan: <a href="#">#78-580</a><br>Korea: Not Available | Power Supply:               |
| Environmental & Durability Factors                                                                                                                                                                                                     |                             |
| 0 to 45                                                                                                                                                                                                                                | Operating Temperature (°C): |
| Red: 625<br>Green: 530<br>Blue: 460<br>White: 6300                                                                                                                                                                                     | Color Temperature (K):      |
| Regulatory Compliance                                                                                                                                                                                                                  |                             |
| <a href="#">View</a>                                                                                                                                                                                                                   | Certificate of Conformance: |

## Product Details

- Heat-Free, Remote Fiber-Optic Illumination
- Designed for Stereo Microscopy and Machine Vision Applications
- Two Light Source Models Available

SCHOTT ColdVision Fiber Optic Illuminators are engineered to deliver uniform light quality while minimizing the thermal impact on illuminated objects. Light sources, light guides, and various mechanical and optical accessories allow for easily customizable illumination based on machine vision or microscopy applications. SCHOTT ColdVision Fiber Optic Illuminators are available in two light source models, the CV-LS series and the MC-LS model. Available in Cool White or RGBW, the CV-LS series contains an optical feedback loop that controls light intensity for consistent, reproducible results in industrial inspection applications. The MC-LS model offers a maximum light intensity of 850 lumens and supports continuous dimming from 0 to 100%, accommodating all levels of stereo microscopy.

**Note:** Power cord sold separately. See specifications for specific products.