

SCHOTT EasyLED Double Spotlight Plus

See More by [SCHOTT Optical Components](#)



SCHOTT EasyLED Double Spotlight Plus



Stock #15-922 3-4 DAYS

- 1 + **£562.70**

ADD TO CART

Qty 1+

£562.70

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Color:
White

Operating Lifetime (hours):
>50,000

Input Voltage (V):
5 DC

Model Number: 600.121
Outer Diameter (mm): 25 (Spot Light Head)
Intensity Control Option: Yes
Output Power (Lumens): 130
Power Supply: Power Supply Required and Sold Separately. USA: #15-907 Europe: #15-907 Japan: #15-907 Korea: #15-907 China: #15-907
Type of Illumination: LED Illuminator
Manufacturer: SCHOTT
Geometry: Spot Light
Illumination Mode: Constant

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View