


SCHOTT KG1, 25mm Dia., 2mm Thick, Colored Glass Heat Absorbing Shortpass Filter

See More by [SCHOTT Optical Components](#)



Stock #19-320 3-4 DAYS

-

1

+

£29.75

ADD TO CART

Qty 1-10

£29.75

Qty 11+

£26.35

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
25.00

Density (g/cm³):
2.53

Glass/Filter Number:

Substrate: □
Heat Absorbing Glass

Operating Temperature (°C):
300 Maximum

Coating:
Uncoated

Index of Refraction n_d:
1.52

Surface Quality:
60-40

Transformation Temperature (°C):
599

Thickness (mm):
2.00 ±0.2

Type:
IR Cut-Off Filter

Dimensional Tolerance (mm):
±0.2

Reflection Factor P_d:
0.92

Wavelength Range (nm):
300 - 2700

Bevel:
Protective as needed

Regulatory Compliance

Certificate of Conformance:
[View](#)