

SCHOTT KG1, 50mm Dia., 2mm Thick, Colored Glass Heat Absorbing Shortpass Filter

See More by [SCHOTT Optical Components](#)



Stock #19-336 3-4 DAYS

⊖

1

⊕

£68.00

ADD TO CART

Qty 1-10

£68.00

Qty 11+

£59.50

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
50.00

Density (g/cm³):
2.53

Glass/Filter Number:

Substrate: □
Heat Absorbing Glass

Operating Temperature (°C):
300 Maximum

Coating:
Uncoated

Index of Refraction n_d:
1.52

Surface Quality:
60-40

Transformation Temperature (°C):
599

Thickness (mm):
2.00 ±0.2

Type:
IR Cut-Off Filter

Dimensional Tolerance (mm):
±0.2

Reflection Factor P_d:
0.92

Wavelength Range (nm):
300 - 2700

Bevel:
Protective as needed

Regulatory Compliance

Certificate of Conformance:
[View](#)