

SCHOTT KG1, 50mm Sq., 3mm Thick, Colored Glass Heat Absorbing Shortpass Filter

See More by [SCHOTT Optical Components](#)



Stock **#14-546** ☐ In Stock

-

1

+

£76.50

ADD TO CART

Qty 1-10

£76.50

Qty 11+

£68.00

Volume Pricing

[Request Quote](#)

 Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Dimensions (mm):
50.0 x 50.0

Density (g/cm³):
2.53

Glass/Filter Number:

[SCHOTT KG1](#)

Substrate: ☐
Heat Absorbing Glass

Length (mm):
50.00

Operating Temperature (°C):
300 Maximum

Coating:
Uncoated

Index of Refraction n_d :
1.52

Surface Quality:
60-40

Transformation Temperature (°C):
599

Thickness (mm):
3.00 ±0.2

Type:
IR Cut-Off Filter

Width (mm):
50.00

Dimensional Tolerance (mm):
±0.2

Reflection Factor P_d :
0.92

Wavelength Range (nm):
300 - 2700

Bevel:
Protective as needed

Regulatory Compliance

RoHS:
[Compliant](#)

Certificate of Conformance:
[View](#)