

SCHOTT KG2, 165 x 165mm, 4.5mm Thick, Matte Colored Glass Filter Plate

See More by [SCHOTT Optical Components](#)



SCHOTT KG Glass (glass color will vary by product specification)

Stock #16-917 3-4 DAYS

-

1

+

£197.20

ADD TO CART

Qty 1-10

£197.20

Qty 11+

£176.80

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Dimensions (mm):
165.0 x 165.0 +3.0/-0.0

Density (g/cm³):
2.52

Glass/Filter Number:
[SCHOTT KG2](#)

Length (mm): 165.00
Coating: Uncoated
Color: Pale Blue-Green
Index of Refraction n_d: 1.51
Transformation Temperature (°C): 605
Thickness (mm): 4.50 ±0.5
Type: IR Cut-Off Filter
Wavelength: VIS
Width (mm): 165.00
Edges: Break Edges
Reflection Factor P_d: 0.92

Regulatory Compliance

Certificate of Conformance: View
--