

# SCHOTT KG5, 50mm Sq., 3mm Thick, Colored Glass Heat Absorbing Shortpass Filter

See More by [SCHOTT Optical Components](#)



Stock #14-555 ▢ In Stock

-

1

+

£76.50

ADD TO CART

Qty 1-10

£76.50

Qty 11+

£68.00

Volume Pricing

[Request Quote](#)

 Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Dimensions (mm):  
50.0 x 50.0

Density (g/cm³):  
2.53

Glass/Filter Number:

SCHOTT KG5

Substrate: ☐  
Heat Absorbing Glass

Length (mm):  
50.00

Operating Temperature (°C):  
300 Maximum

Coating:  
Uncoated

Index of Refraction  $n_d$ :  
1.51

Surface Quality:  
60-40

Transformation Temperature (°C):  
565

Thickness (mm):  
3.00 ±0.2

Type:  
IR Cut-Off Filter

Width (mm):  
50.00

Dimensional Tolerance (mm):  
±0.2

Reflection Factor  $P_d$ :  
0.92

Wavelength Range (nm):  
300 - 2700

Bevel:  
Protective as needed

Regulatory Compliance

RoHS:  
Compliant

Reach 223:  
Compliant

Certificate of Conformance:  
[View](#)