

SCHOTT NG4, 165 x 165mm, 4.5mm Thick, Matte Colored Glass Filter Plate

See More by [SCHOTT Optical Components](#)



SCHOTT NG Glass (glass color will vary by product specification)

Stock **#16-922** 3-4 DAYS

- 1 + **£240.55**

ADD TO CART

Qty 1-10
£240.55
Qty 11+
£216.75
Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads
Dimensions (mm): 165.0 x 165.0 +3.0/-0.0
Density (g/cm³): 2.43
Glass/Filter Number: SCHOTT NG4

Length (mm): 165.00
Coating: Uncoated
Color: Gray
Index of Refraction n_d: 1.51
Transformation Temperature (°C): 483
Thickness (mm): 4.50 ±0.5
Type: Neutral Density Filter
Wavelength: VIS
Width (mm): 165.00
Edges: Break Edges
Reflection Factor P_d: 0.92

Regulatory Compliance

Reach 224: Compliant
Certificate of Conformance: View