

SCHOTT RG780, 165 x 165mm, 4.5mm Thick, Matte Colored Glass Filter Plate

See More by [SCHOTT Optical Components](#)



SCHOTT RG Glass (glass color will vary by product specification)

Stock **#16-938** 3-4 DAYS

-

1

+

£360.40

ADD TO CART

Qty 1-10
£360.40
Qty 11+
£324.70
Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Dimensions (mm):
165.0 x 165.0 +3.0/-0.0

Density (g/cm³):
2.94

Glass/Filter Number:
[SCHOTT RG780](#)

Length (mm): 165.00
Coating: Uncoated
Color: Black
Index of Refraction n_d: 1.56
Transformation Temperature (°C): 552
Thickness (mm): 4.50 ±0.5
Type: Longpass Filter
Wavelength: IR
Width (mm): 165.00
Edges: Break Edges
Reflection Factor P_d: 0.91

Regulatory Compliance

Certificate of Conformance: View
--