

SCHOTT RG9, 165 x 165mm, 4.5mm Thick, Matte Colored Glass Filter Plate

See More by [SCHOTT Optical Components](#)



SCHOTT RG9 Glass (glass color will vary by product specification)

Stock **#16-931** 3-4 DAYS

- 1 + **£223.55**

ADD TO CART

Qty 1-10
£223.55
Qty 11+
£200.60
Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads
Dimensions (mm): 165.0 x 165.0 +3.0/-0.0
Density (g/cm³): 2.58
Glass/Filter Number: SCHOTT RG9

Length (mm): 165.00
Coating: Uncoated
Color: Black
Index of Refraction n_d: 1.52
Transformation Temperature (°C): 519
Thickness (mm): 4.50 ±0.5
Type: Longpass Filter
Wavelength: IR
Width (mm): 165.00
Edges: Break Edges
Reflection Factor P_d: 0.92

Regulatory Compliance

Certificate of Conformance: View
--