

SCHOTT UG11, 12.5mm Dia., 2mm Thick, Colored Glass Bandpass Filter

See More by [SCHOTT Optical Components](#)



Stock **#16-372** 3-4 DAYS

[Additional Bandwidths](#)

1

£39.95

ADD TO CART

Qty 1-10

£39.95

Qty 11+

£34.85

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
12.50

Center Wavelength CWL (nm):
325.00

Density (g/cm³): 2.92
Glass/Filter Number: SCHOTT UG11
Coating: Uncoated
Color: Black
Index of Refraction n_d: 1.56
Surface Quality: 60-40
Transformation Temperature (°C): 545
Thickness (mm): 2.00 ±0.2
Type: Bandpass Filter
Wavelength: UV
Bevel: Protective as needed

Regulatory Compliance

Certificate of Conformance: View
--