

# SCHOTT UG11, 50mm Sq., 3mm Thick, Colored Glass Bandpass Filter

See More by [SCHOTT Optical Components](#)



Stock **#14-456** ☐ In Stock



1



£144.50

ADD TO CART

|                               |
|-------------------------------|
| Qty 1-10                      |
| £144.50                       |
| Qty 11+                       |
| £129.20                       |
| Volume Pricing                |
| <a href="#">Request Quote</a> |

ⓘ Prices shown are exclusive of VAT/local taxes

## Get Product Downloads

**Dimensions (mm):**  
50.0 x 50.0

**Center Wavelength CWL (nm):**  
325.00

|                                                            |
|------------------------------------------------------------|
| <b>Density (g/cm³):</b><br>2.92                            |
| <b>Glass/Filter Number:</b><br><a href="#">SCHOTT UG11</a> |
| <b>Length (mm):</b><br>50.00                               |
| <b>Coating:</b><br>Uncoated                                |
| <b>Color:</b><br>Black                                     |
| <b>Index of Refraction <math>n_d</math>:</b><br>1.56       |
| <b>Surface Quality:</b><br>60-40                           |
| <b>Transformation Temperature (°C):</b><br>545             |
| <b>Thickness (mm):</b><br>3.00 ±0.2                        |
| <b>Type:</b><br>Bandpass Filter                            |
| <b>Wavelength:</b><br>UV                                   |
| <b>Width (mm):</b><br>50.00                                |
| <b>Bevel:</b><br>Protective as needed                      |

Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS:</b><br><a href="#">Compliant</a>                  |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |