

SCHOTT VG9, 12.5mm Dia., 3mm Thick, Colored Glass Bandpass Filter

See More by [SCHOTT Optical Components](#)



Stock **#16-401** ☐ In Stock

[Additional Bandwidths](#)

-

1

+

£34.85

ADD TO CART

Qty 1-10

£34.85

Qty 11+

£31.45

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
12.50

Center Wavelength CWL (nm):
525.00

Density (g/cm³): 2.87
Glass/Filter Number: SCHOTT VG9
Coating: Uncoated
Color: Green
Index of Refraction n_d: 1.55
Surface Quality: 60-40
Transformation Temperature (°C): 462
Thickness (mm): 3.00 ±0.2
Type: Bandpass Filter
Wavelength: VS
Bevel: Protective as needed

Regulatory Compliance

Certificate of Conformance: View
--