

TECHSPEC®

Sliding 2" x 3" Base Plate Slot



Stock

#52-083

20+ In Stock

-

1

+

£20¹⁴

ADD TO CART

Volume Pricing	
Qty 1-9	£20.14 each
Qty 10+	£17.86 each
Need More?	Request Quote

Prices shown are exclusive of VAT/local taxes

Product Downloads

SPECIFICATIONS

General

English

Type:

Physical & Mechanical Properties

76.20	Length (mm):
50.80	Width (mm):
9.50	Thickness (mm):
Black Anodized Aluminum	Construction:
2	Number of Slots:

Regulatory Compliance

CompliantRoHS 2015:

ViewCertificate of Conformance:

CompliantReach 250:

PRODUCT DETAILS

- Increase the Versatility of Existing Mounting Equipment
- Ideal for Direct Mounting to Standard Breadboards
- Counterbored 1/4-20 or M6 x 1.0 Holes/Slots

TECHSPEC® Slotted 2" x 3" Base Plates are versatile mounting surfaces for breadboard and optical rail applications. Three 6.4mm diameter counterbored holes, ideal for 1/4"-20 hardware, allow posts or post holders to be mounted directly and can also accommodate a variety of other optomechanical components. The plates are ideal for adding extra versatility and adjustment capability to a benchtop optical system. TECHSPEC® Slotted 2" x 3" Base Plates are available in standard sliding or side to side sliding configurations, allowing for adjustment along or perpendicular to the optical axis of the system.

TECHNICAL INFORMATION

