

[See all 13 Products in Family](#)

TECHSPEC[®]

T-Mount, 60mm x 85mm Plate Mount, M6



Stock **#65-983** 2 In Stock

-

1

+

£424^{.00}

ADD TO CART

Volume Pricing	
Qty 1-4	£424.00 each
Qty 5-9	£374.80 each
Qty 10-25	£345.28 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Optic Mount (Fixed)

Function:

Rectangular

Type of Optics:

Includes four T-Mount Aperture Caps ([#66-037](#))

Note:

Dimensions of Compatible Optics (mm):

60.0 x 85.0

Physical & Mechanical Properties

75.0 x 75.0 x 75.0
Dimensions (mm):

75.0
Extension Length (mm):

1.0
Min. Thickness of Compatible Optics (mm):

4.73
Max. Thickness of Compatible Optics (mm):

Threading & Mounting

T-Mount
Thread Type:

M6 x 1.0
Compatible Post:

Regulatory Compliance

Compliant
RoHS 2015:

View
Certificate of Conformance:

Compliant
Reach 233:

Product Details

- C, S, and T-Mount Solutions for Mounting Cube and Plate Beamsplitters, Filters, and Mirrors
- Provides a 90° Mounting Interface
- ¼-20 and M6 Tapped Mounting Threads for English or Metric Based Systems

TECHSPEC® C, S, and T-Mount Cube and Plate Mounts allow for the integration of cube and plate optics into C, S, and T-Mount systems. These mounts feature four C, S, or T-Mount threaded apertures that can also act as connection points for other C, S, or T-Mount components. Either an M6 or 1/4-20 tapped hole is provided on the base for post mounting, making these mounts compatible with breadboard and benchtop systems. TECHSPEC C, S, and T-Mount Cube and Plate Mounts provide a 90° mounting interface ideal for placing beamsplitters, filters, and mirrors within a system. C, S, and T-Mount Aperture Caps are available to block light from unused openings and to protect the optic from dust and debris.

Note: #11-139 and #11-142 each include one S-Mount Aperture Cap (#11-137)

Technical Information

