

Tip Kit, 8 piece Dissipative Straight



Representative Picture of Straight and Bent Probes

Stock **#57-646** **8 In Stock**

⊖ 1 ⊕ £41²⁰

ADD TO CART

Volume Pricing

| | |
|------------|-------------------------------|
| Qty 1+ | £41.20 each |
| Need More? | Request Quote |

! Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Contents of Kit:

8 straight probes: 3/32", 1/8", 3/16", 1/4", 3/8", 1/2", 5/8", 3/4"

Regulatory Compliance

[Compliant](#)

Reach 191:

[Compliant](#)

RoHS 2015:

Product Details

- ESD-Safe
- Pen and Bulb Options
- General-Purpose Component Handling

Handi-Vac® and Pen-Vac® Pick-up Tool Kits feature lightweight, economical tools with black dissipative plastic handles and are available with non-marring static dissipative or conductive silicon vacuum cups. Placement accuracy is not as precise as a pen-style pick-up tool, but the bulb-style model is cost-effective enough to include in every tool kit. Simply squeeze the Handi-Vac® handle (bladder) for suction or press/release the Pen-Vac® push button to control the vacuum. Handi-Vac® and Pen-Vac® Pick-up Tool Kits have probes with stainless steel stems with zinc fittings. Black cups have a 0.035" inner diameter on the component side and can be directly mounted to the handle.

Handi-Vac® Kits include 4 interchangeable tips (OD cup size): 1/8" (one bent & one straight probe), 1/4" with bent probe, and 3/8" with straight probe. Pen-Vac® Kits include 6 tips, in the same sizes, each with one bent and one straight probe.

Tip Kits come with 8 straight probes: 3/32", 1/8", 3/16", 1/4", 3/8", 1/2", 5/8", 3/4" (OD cup size)
