

Ti:Sapphire Variable Ultrafast Pulse Compressor, 780 - 830nm



Stock **#26-397** [CONTACT US](#)

- 1 + **£6,892.65**

ADD TO CART

Qty 1+
£6,892.65

Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Polarization:
p

Dimensions (inches):
9 x 8 x 4

Wavelength Range (nm):
780 - 830

GDD Specification (fs²):
-10400 to -2600

Input Beam Diameter, 1/e² (mm):
2 (maximum)

Minimum Efficiency (%):

97.60

GDD Increment (fs²):

-2600

Regulatory Compliance

RoHS:

Compliant

Certificate of Conformance:

[View](#)