

Two-Axis Adjustable Slit



2-Axis Adjustable Slits

Stock **#29-312** [CONTACT US](#)

-

1

+

£532⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	£532.00 each
Need More?	Request Quote

 Prices shown are exclusive of VAT/local taxes

Product Downloads

Physical & Mechanical Properties	
10 x 10	Maximum Aperture (mm):
50	Outer Diameter (mm):
10.00	Thickness (mm):
Threading & Mounting	
	Mounting Threads:

M2 x0.4	
Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 247:

Product Details

- Two Independently Adjustable Axes
- Any Rectangular Slit Size up to 10 x 10mm
- 50mm Outer Diameter for Ease of System Integration

Two-Axis Adjustable Slits feature two independently adjustable mechanical levers for use in multi-axis beam shaping applications. The slits open evenly from fully closed to a 10 x 10mm square. Featuring a 50mm outer diameter, 10mm thickness, and two M2 mounting holes on its face, the Two-Axis Adjustable Slit can be easily integrated into benchtop optical applications. These slits are ideal for applications including light spectrophotometer image analysis, lensless imaging and multi axis beam shaping.