



# Hoya U360 (UV) 25mm Square, Colored Glass Bandpass Filter

See More by [Hoya](#)



Stock **#46-085** 3-4 DAYS

-

1

+

**£67.15**

ADD TO CART

Qty 1-10

£67.15

Qty 11+

£59.50

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Dimensions (mm):  
25.0 x 25.0

Center Wavelength CWL (nm):

|                                                      |
|------------------------------------------------------|
| 360.00                                               |
| Density (g/cm³):<br>2.74                             |
| Full Width-Half Max FWHM (nm):<br>45.00              |
| Glass/Filter Number:<br><a href="#">Hoya U360</a>    |
| Substrate: <input type="checkbox"/><br>Colored Glass |
| Length (mm):<br>25.00                                |
| Coating:<br>Uncoated                                 |
| Color:<br>Black                                      |
| Surface Quality:<br>80-50                            |
| Thickness (mm):<br>2.50                              |
| Thickness Tolerance (mm):<br>±0.2                    |
| Type:<br>Bandpass Filter                             |
| Wavelength:<br>UV                                    |
| Width (mm):<br>25.00                                 |
| Parallelism (arcmin):<br>≤1                          |
| Dimensional Tolerance (mm):<br>+0/-0.25              |

Regulatory Compliance

|                                                     |
|-----------------------------------------------------|
| RoHS 2015:<br><a href="#">Exempt</a>                |
| Reach 224:<br><a href="#">Compliant</a>             |
| Certificate of Conformance:<br><a href="#">View</a> |