

[See all 104 Products in Family](#)

IDS U3-3070CP-M-GL, USB 3.0, 1/1.8" Monochrome Camera

See More by [IDS Imaging Development Systems](#)



IDS Imaging uEye+ USB3 Camera, CP Model (Front)



Stock **#16-513** **1 In Stock**

[Similar Cameras](#)

-

1

+

£816^{.00}

ADD TO CART

Volume Pricing	
Qty 1+	£816.00 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Note: This item requires accessories for use | [Learn More](#)

Product Downloads

Monochrome

Spectrum:

General

Monochrome Camera

Type:

U3-3070CP-M-GL	Model Number:
IDS Imaging Development Systems	Manufacturer:
uEye+ CP	Camera Series:

Physical & Mechanical Properties

29 x 29 x 29 (excludes connectors and lens mount)	Dimensions (mm):
50	Weight (g):
Full	Housing:

Sensor

128MB	Image Buffer:
1/1.8"	Sensor Format:
3.15	Resolution (Megapixels):
114.00	Frame Rate (fps):
2,056 x 1,542	Pixels (H x V):
3.45 x 3.45	Pixel Size, H x V (µm):
7.093 x 5.32	Sensing Area, H x V (mm):
Sony IMX252	Imaging Sensor:
Progressive Scan CMOS	Type of Sensor:
Global	Shutter Type:
12 bit	Pixel Depth:
0.025ms - 2000ms	Exposure Time:
70.00	Dynamic Range (dB):
USB3 Vision	Machine Vision Standard:

Electrical

1.6 - 3.5	Power Consumption (W):
-----------	------------------------

Hardware & Interface Connectivity

USB 3.0	Interface:
USB 3.0 micro-B, screwable	Connector:
Power over USB	Power Supply:
2 Flash Output, 2 Trigger Input, 2 GPIO, 1 Output Supply Voltage, 1 Ground	GPIOs:
Hardware Trigger (GPIO)	Synchronization:
Back Panel	Interface Port Orientation:
8-pin Hirose connector (HR25-7TR-8PA(73))	GPIO Connector Type:

Threading & Mounting

C-Mount	Mount:
1/4-20 with Tripod Mount Adapter #35-088	Mounting Threads:

Environmental & Durability Factors

0 to +55	Operating Temperature (°C):
----------	-----------------------------

Storage Temperature (°C):	
-20 to +60	
Regulatory Compliance	
Exempt	RoHS 2015:
View	Certificate of Conformance:
REACH 241:	
Contains SVHC(s)	

Product Details

- Standard (SE), Compact (CP), and Ultra Compact (XCP) Housing Options Available
- C-Mount with Large Format CMOS Sensors up to 1.1"
- Up to 20.44MP Resolution with Framerrates up to 396fps

IDS Imaging uEye CP/XCP/SE USB3 Cameras utilize [IDS Imaging's peak SDK platform](#) that supports GeniCam and USB3 Vision standards for easy software development and integration. The CP cameras are the industry standard size of 29 x 29 x 29mm and work for almost any application. The XCP cameras have an ultra-compact size of 29 x 29 x 17mm and are an excellent option for price-sensitive, single-camera applications. The SE cameras have a larger housing size of 34 x 44 x 47mm to allow for exceptional heat management and are ideal for noise and heat-sensitive applications. IDS Imaging uEye CP/XCP/SE USB3 Cameras are ideal for manufacturing, industrial, and automation applications.