

Universal Right Angle Bracket



Universal Right Angle Bracket (#11-157)

Stock **#11-157** **2 In Stock**

-

1

+

£133⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	£133.60 each
Need More?	Request Quote

! Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Universal

Type:

Physical & Mechanical Properties

1.0

Thickness (inches):

6.0

Width (inches):

Construction:

Black Anodized Aluminum	
Length (inches):	
12.0	
Threading & Mounting	
Mounting Threads:	
(9) 1/4-20 (M6x1.0) S.H.C.S. Thru-Slots	
Regulatory Compliance	
RoHS 2015:	
Compliant	
Certificate of Conformance:	
View	
Reach 250:	
Compliant	

Product Details

- Universal Design Works With Metric and English Bench Plates and Breadboards
- Uses Standard 1/4-20 or M6 Socket Head Cap Screws
- Black Anodized Aluminum Construction

Universal Right Angle Brackets allow our English and Metric Economical Bench Plates to be mounted orthogonally to a Composite Breadboard or another bench plate. These brackets are made from 1" thick black anodized aluminum. Thru-slots on the vertical and horizontal arms of the bracket allow for the use of both M6 and 1/4-20 SHCS for mounting, and accommodate breadboard hole spacing of 1" and 25mm. Universal Right Angle Brackets feature a ubiquitous design that enables easy integration of additional components into any benchtop system. For applications that require more structural support, purchase the Universal Right Angle Bracket, Pair ([#11-158](#)).

Note: Not recommended for use with plates taller than 12" or 300mm.

Technical Information

