


V-Block Base with Clamps



Stock #03-665 12 In Stock

-

1

+

£244^{.00}

ADD TO CART

Volume Pricing	
Qty 1-4	£244.00 each
Qty 5-9	£215.84 each
Qty 10-49	£198.80 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Fixed

Type:

Cylindrical Tube

Type of Optics:

Physical & Mechanical Properties

Construction:

Black Anodized Aluminum, Stainless Steel Post


2	Number of Clamps:
Threading & Mounting	
5.6 - 67.9	Size of Compatible Optics (mm):
1/4-20	Compatible Post:
Regulatory Compliance	
Compliant	RoHS 2015:
Compliant	Reach 224:
View	Certificate of Conformance:

Product Details

- Adjustable Height Bar Clamp Included with [#03-665](#)
- Ideal for Mounting Laser Tubes and Large Optical Elements
- 1/4-20 Tap Hole Allows Mounting to 0.50" Diameter Post

Our V-Block base is ideal for mounting laser tubes and optical elements thick enough to stand vertically on edge (such as most achromats). The six 1/4-20 tap holes around the base are designed to accept clamp posts, but may also be used to mount the V-Block. A 1/4-20 tap hole in the center of the base allows mounting to any 0.50" diameter post. Adjustable height bar-type clamp secures components in the V-Block.

Technical Information



V-Block Base