

White 150mm Compact Light w/ Dual OverDrive™



150mm Compact Light



Stock **#23-943** **1 In Stock**

⊖ 1 ⊕ £568⁰⁰

ADD TO CART

Volume Pricing

Qty 1+	£568.00 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

JWL150-DO-WHI **Model Number:**

LED Illuminator **Type of Illumination:**

Smart Vision Lights LLC **Manufacturer:**

Ring Light

Geometry:

Constant or Strobed

Illumination Mode:

Physical & Mechanical Properties

Dimensions (mm):
158.75 W x 84.25 H x 40.18 D (58.15 D Including Connector)

Weight (g):
589.67

Active Area (mm):
65.38W x 65.38W

Optical Properties

Color:
White

Working Distance (mm):
500 - 2,000

Electrical

Strobe Duration (µs):
10 - 7,000

Hardware & Interface Connectivity

Connector:
5-pin M12 connector

Input Voltage (V):
24 VDC ± 5%

Threading & Mounting

Mount:
T-Slot for M6 Nut

Environmental & Durability Factors

Operating Temperature (°C):
-10° to +40°

Environmental Rating:
IP65

Regulatory Compliance

Certificate of Conformance:
[View](#)

Product Details

- Utilize Dual OverDrive™ Technology for 10x Standard Light Output
- Offer Illumination Coverage over a Larger Field of View
- Direct Connect and Control via Camera's Trigger Output
- Ideal for High Speed Logistics Applications

Smart Vision Lights High Output Ring Lights are IP65-rated brightfield lights featuring a working distance of 500-mm to 2000-mm that can be directly connected to a camera for control via the trigger output. Built-in Dual OverDrive™ technology, which delivers up to 6 times the continuous power with a low-latency response and fast strobe durations down to 10ms. These lights feature a batwing design that illuminates a larger area than built-in lighting systems and produces a greater light output making them ideal to use alongside polarizers, diffusers, and other optical elements that reduce light output. Smart Visions Lights Illumination products offer an industry-leading 10-year limited warranty.