

Hoya Y50 (500nm), 12.5mm Dia., 2.5mm Thick, Colored Glass Longpass Filter

See More by [Hoya](#)



Stock #66-039 3-4 DAYS

⊖ 1 ⊕ **£27.20**

ADD TO CART

Qty 1-10
£27.20

Qty 11+
£23.80

Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
12.50

Cut-Off Position λ_c (nm):
500±6

Cut-On Wavelength (nm):
500.00 ±6

Density (g/cm³): 2.68
Glass/Filter Number: Hoya Y50
Substrate: ☐ Colored Glass
Coating: Uncoated
Color: Yellow
Surface Quality: 80-50
Transformation Temperature (°C): 560
Thickness (mm): 2.50
Thickness Tolerance (mm): ±0.2
Type: Longpass Filter
Wavelength: VS
Dimensional Tolerance (mm): ±0.38
Reflection Factor P _d : 0.92
Bevel: Protective as needed
Δλ (nm): <25
TH (%): >85

Regulatory Compliance

RoHS 2015: Exempt
Reach 224: Compliant
Certificate of Conformance: View