

Z-Axis Plate for 1.25" Stage (Center Drive-Low Profile)



Stock **#54-367** [CONTACT US](#)

-

1

+

£115^{.20}

ADD TO CART

Volume Pricing	
Qty 1+	£115.20 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Low Profile		Note:
1.25		Compatible Stage Size (inches):

Center Drive		Stage Type:
--------------	--	-------------

Physical & Mechanical Properties

1.25		Length (inches):
------	--	------------------

1.25	Width (inches):
1.63	Thickness (inches):
None	Bracket Thru-Hole:

Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:

Product Details

- Combine Ball Bearing Stages into 3 Axis Positioning Systems
- Designs for 1.25, 1.75, 2.62, and 5" Stages
- Aluminum Construction with Black Anodized Finish

We now offer a complete line of Z-axis brackets to combine ball bearing stages into three axis positioning systems. These brackets are currently included with all X-Y-Z low and standard profile stage configurations. By purchasing single-axis stages separately, the brackets can be used to configure your own X-Y-Z combination, using different drive options, travel options, and even standard or thru-hole mounting stage options. All brackets are designed for the same stage size and drive type (center or side). All Z-axis brackets include socket head cap screws (S.H.C.S.) to connect two ball bearing stages together; 4 screws for each bracket ([#54-380](#) includes 6 screws; 2-Z, 4-Y). Brackets are designed for Z-axis mounting with tapped mounting holes to accept screws through the counterbored holes in stage bases. Y-axis mounting on the brackets is with clearance or counterbored holes for S.H.C.S. to connect directly to stage carriage mounting surfaces. Aluminum construction with black anodized finish. X-Y and X-Z configurations are possible. However, due to side locking screws and mounting stage configurations, not all options will work. All standard profile brackets have thru-hole clearance.

Note: [#54-374](#) Z-Axis Plate for 1.75" Stages is for use with 1" or 25mm travel stages: [#37-935](#), [#37-936](#), [#37-955](#), and [#37-956](#).

Technical Information

