

Zero Aperture, 75mm Max. Aperture, Iris Diaphragm



Stock **#64-506** [CONTACT US](#)

-

1

+

£190⁴⁰

ADD TO CART

Volume Pricing	
Qty 1-9	£190.40 each
Qty 10-25	£168.56 each
Qty 26+	£155.68 each
Need More?	Request Quote

i Prices shown are exclusive of VAT/local taxes

Product Downloads

General	
Unmounted	Type:
Physical & Mechanical Properties	
Maximum Aperture (mm):	

75.0	
102.0	Outer Diameter (mm):
Construction: Black Anodized Aluminum, Black Spring Steel Leaves, Stainless Steel Pins	
3.00	Lever Diameter (mm):
14.50	Lever Length (mm):
Two Sets of 10	Number of Leaves:
3.5	Spacing of Leaf Layers (mm):
9.10	Thickness (mm):

Optical Properties	
0.00	Minimum Aperture (mm):

Regulatory Compliance	
Exempt	RoHS 2015:
View	Certificate of Conformance:
Contains SVHC(s)	Reach 247:

Product Details

• Provide Total Light Extinction When Closed

• Aperture Sizes Up to 75mm

• Mounted Options Available

Zero Aperture Series Iris Diaphragms are designed and manufactured using the same high-quality movements as our [Standard Series Iris Diaphragms](#) but with the added benefit of total light extinction. This type of control is often used in systems where the dark signal (background noise) must be measured for calibration. For each iris, there are two additional relief leaves (not listed in table) that are not visible. These diaphragms are offered with maximum apertures of 12 – 75mm and have outer diameters ranging from 21 to 102mm. Zero Aperture Series Iris Diaphragms feature two sets of leaves which are mounted on different tiers and are moved by one lever.

For specific OEM application assistance, please contact our [Applications Engineering Department](#).

Note: [Iris Diaphragm Mounts](#) sold separately.

Technical Information

Outer Diameter A	Maximum Aperture B	Minimum Aperture C	Thickness D	Stock No.
102mm	75mm	0mm	9.1mm	#64-506
21mm	12mm		6.2mm	#53-906
29mm	12mm		6.1mm	#62-649
38mm	25mm			#53-907
54mm	37mm		7.5mm	#53-908
72mm	50mm		9.1mm	#53-909
37mm	12mm		6.2mm	#62-653
54mm	25mm		6.1mm	#62-654
67mm	37mm		7.5mm	#62-655
88mm	50mm		9.1mm	#62-656

Zero Aperture Series Iris Diaphragms

The diagram illustrates the Zero Aperture Series Iris Diaphragms. The top view shows a circular iris with multiple segments, a central lever actuator, and a 90° rotation arrow. Dimensions B and C are indicated for the top view. The side view shows the thickness D and the lever actuator. Dimension A is indicated for the side view.

Units: mm