

## Zero Aperture, 25mm Max. Aperture, Mounted Iris Diaphragm



Stock #62-654 3-4 DAYS

- 1 + **£78.20**

ADD TO CART

|                               |
|-------------------------------|
| Qty 1-9                       |
| £78.20                        |
| Qty 10+                       |
| £69.27                        |
| Volume Pricing                |
| <a href="#">Request Quote</a> |

⚠ Prices shown are exclusive of VAT/local taxes

|                                |
|--------------------------------|
| Get Product Downloads          |
| Type:<br>Mounted               |
| Minimum Aperture (mm):<br>0.00 |
| Maximum Aperture (mm):         |

|                                                                                                     |
|-----------------------------------------------------------------------------------------------------|
| 25.0                                                                                                |
| <b>Outer Diameter (mm):</b><br>52.0                                                                 |
| <b>Construction:</b><br>Black Anodized Aluminum, Black Spring Steel Leaves,<br>Stainless Steel Pins |
| <b>Lever Diameter (mm):</b><br>3.00                                                                 |
| <b>Lever Length (mm):</b><br>12.80                                                                  |
| <b>Number of Leaves:</b><br>Two Sets of 7                                                           |
| <b>Spacing of Leaf Layers (mm):</b><br>2.4                                                          |
| <b>Thickness (mm):</b><br>9.50                                                                      |

Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Exempt</a>                |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |
| <b>Reach 235:</b><br><a href="#">Contains SVHC(s)</a>      |