

Zero Aperture, 50mm Max. Aperture, Mounted Iris Diaphragm



Stock #62-656 [CONTACT US](#)

-

1

+

£173.40

ADD TO CART

Qty 1-9
£173.40
Qty 10+
£152.91
Volume Pricing
Request Quote

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads
Type: Mounted
Minimum Aperture (mm): 0.00
Maximum Aperture (mm):

50.0
Outer Diameter (mm): 88.0
Construction: Black Anodized Aluminum, Black Spring Steel Leaves, Stainless Steel Pins
Lever Diameter (mm): 3.00
Lever Length (mm): 13.50
Number of Leaves: Two Sets of 8
Spacing of Leaf Layers (mm): 3.2
Thickness (mm): 11.50

Regulatory Compliance

RoHS 2015: Exempt
Certificate of Conformance: View
Reach 235: Contains SVHC(s)