SCHOTT BG25, 50mm Sq., 2mm Thick, Colored Glass Bandpass Filter

See More by SCHOTT Optical Components



Stock **#14-413** In Stock

- 1 + **£74.80**

ADD TO CART

Qty 1-10
£74.80

Qty 11+
£66.30

Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Dimensions (mm):
50.0 x 50.0

Center Wavelength CWL (nm):
400.00

Density (g/cm^3):
2.56

Glass/Filter Number:
SCHOTT BG25

Length (mm):
50.00

Coating:
Uncoated

Color:
Blue-Violet

Index of Refraction n_d:
1.51

Surface Quality:
60-40

Transformation Temperature (°C):
487

Thickness (mm):
2.00 ±0.2

Type:
Bandpass Filter

Wavelength:
UV-VIS

Width (mm):
50.00

Bevel:
Protective as needed

Regulatory Compliance

RoHS:
Compliant

Certificate of Conformance:
View