

[All Products](#) / [Optics](#) / [Optical Lenses](#) / [Plano-Convex \(PCX\) Lenses](#) / [Standard Plano-Convex \(PCX\) Lenses](#)

TECHSPEC® VIS-NIR Coated Plano-Convex (PCX) Lenses



- AR Coated to Provide <1.25% Reflectance per Surface for 400 - 1000nm
- <0.25% Reflectance @ 880nm
- Designed for 0° Angle of Incidence
- Various PCX Coating Options: [Uncoated](#), [MgF₂](#), [VIS 0°](#), [NIR I](#), [NIR II](#), [VIS-EXT](#), and [YAG-BBAR](#)

Common Specifications

Physical & Mechanical Properties

Bevel: Protective as needed



Optical Properties

Coating: VIS-NIR (400-1000nm)

Focal Length Tolerance (%): ± 1

Wavelength Range (nm): 400 - 1000

Technical Information



Products

Dia. (mm)	EFL (mm)	BFL (mm)	Coating	Substrate	Stock Number	Price	Buy
1.00	0.60	0.17	VIS-NIR (400-1000nm)	N-LASF9	#65-289	£71.35 Volume Pricing	5 In Stock
1.00	1.00	0.57	VIS-NIR (400-1000nm)	N-LASF9	#65-290	£71.35 Volume Pricing	5 In Stock
1.00	1.50	1.07	VIS-NIR (400-1000nm)	N-LASF9	#65-291	£71.35 Volume Pricing	Contact Us
1.00	2.00	1.57	VIS-NIR (400-1000nm)	N-LASF9	#65-292	£71.35 Volume Pricing	6 In Stock
1.50	1.00	0.57	VIS-NIR (400-1000nm)	N-LASF9	#65-293	£71.35 Volume Pricing	5 In Stock
1.50	1.50	1.07	VIS-NIR (400-1000nm)	N-LASF9	#65-294	£71.35 Volume Pricing	3 In Stock
1.50	2.00	1.57	VIS-NIR (400-1000nm)	N-LASF9	#65-295	£71.35 Volume Pricing	17 In Stock
2.00	1.50	1.07	VIS-NIR (400-1000nm)	N-LASF9	#65-296	£70.47 Volume Pricing	20+ In Stock
2.00	2.00	1.57	VIS-NIR (400-1000nm)	N-LASF9	#65-297	£70.47 Volume Pricing	20+ In Stock
2.00	3.00	2.57	VIS-NIR (400-1000nm)	N-LASF9	#65-298	£70.47 Volume Pricing	5 In Stock
2.00	4.00	3.57	VIS-NIR (400-1000nm)	N-LASF9	#65-299	£70.47 Volume Pricing	4 In Stock
2.50	2.00	1.57	VIS-NIR (400-1000nm)	N-LASF9	#65-300	£70.47 Volume Pricing	2 In Stock

2.50	2.50	2.05	VIS-NIR (400-1000nm)	N-LASF9	#65-301	£70.47 Volume Pricing	10 In Stock
2.50	3.00	2.57	VIS-NIR (400-1000nm)	N-LASF9	#65-302	£70.47 Volume Pricing	20+ In Stock
2.50	4.00	3.57	VIS-NIR (400-1000nm)	N-LASF9	#65-303	£70.47 Volume Pricing	10 In Stock
2.50	5.00	4.57	VIS-NIR (400-1000nm)	N-LASF9	#65-304	£70.47 Volume Pricing	13 In Stock
3.00	3.00	1.88	VIS-NIR (400-1000nm)	N-SF11	#49-174	£60.41 Volume Pricing	7 In Stock
3.00	4.50	3.50	VIS-NIR (400-1000nm)	N-LASF44	#49-175	£60.41 Volume Pricing	20+ In Stock
3.00	6.00	4.81	VIS-NIR (400-1000nm)	N-BK7	#49-176	£56.03 Volume Pricing	3 In Stock
3.00	7.50	6.51	VIS-NIR (400-1000nm)	N-BK7	#49-177	£56.03 Volume Pricing	20+ In Stock
3.00	9.00	8.01	VIS-NIR (400-1000nm)	N-BK7	#49-178	£56.03 Volume Pricing	20+ In Stock
3.00	12.00	11.29	VIS-NIR (400-1000nm)	N-BK7	#49-179	£56.03 Volume Pricing	10 In Stock
3.00	15.00	14.17	VIS-NIR (400-1000nm)	N-BK7	#49-180	£56.03 Volume Pricing	5 In Stock
4.00	4.00	3.06	VIS-NIR (400-1000nm)	N-LASF44	#47-850	£60.41 Volume Pricing	8 In Stock
4.00	6.00	4.51	VIS-NIR (400-1000nm)	N-BK7	#47-851	£60.41 Volume Pricing	20+ In Stock
4.00	8.00	7.17	VIS-NIR (400-1000nm)	N-BAF10	#47-852	£56.91 Volume Pricing	Contact Us

4.00	10.00	8.92	VIS-NIR (400-1000nm)	N-BK7	#47-853	£56.91 Volume Pricing	20+ In Stock
4.00	12.00	11.00	VIS-NIR (400-1000nm)	N-BK7	#47-854	£56.91 Volume Pricing	Contact Us
4.50	4.50	3.05	VIS-NIR (400-1000nm)	N-LASF44	#47-855	£60.41 Volume Pricing	20+ In Stock
4.50	9.00	7.41	VIS-NIR (400-1000nm)	N-BK7	#47-856	£56.91 Volume Pricing	7 In Stock
5.00	5.00	3.96	VIS-NIR (400-1000nm)	N-LASF44	#47-857	£44.43 Volume Pricing	20+ In Stock
5.00	7.50	6.43	VIS-NIR (400-1000nm)	N-SF11	#48-661	£43.99 Volume Pricing	13 In Stock
5.00	10.00	8.91	VIS-NIR (400-1000nm)	N-BK7	#47-858	£43.99 Volume Pricing	2 In Stock
5.00	12.00	10.83	VIS-NIR (400-1000nm)	N-BK7	#47-859	£43.99 Volume Pricing	6 In Stock
5.00	15.00	13.94	VIS-NIR (400-1000nm)	N-BK7	#47-860	£43.99 Volume Pricing	Contact Us
5.00	20.00	19.02	VIS-NIR (400-1000nm)	N-BK7	#49-913	£43.99 Volume Pricing	5 In Stock
5.00	25.00	23.95	VIS-NIR (400-1000nm)	N-BK7	#87-917	£43.99 Volume Pricing	2 In Stock
5.00	30.00	28.95	VIS-NIR (400-1000nm)	N-BK7	#87-918	£43.99 Volume Pricing	1 In Stock
6.00	6.00	4.60	VIS-NIR (400-1000nm)	N-SF11	#45-465	£37.21 Volume Pricing	1 In Stock
6.00	7.50	6.10	VIS-NIR (400-1000nm)	N-SF11	#49-914	£36.77 Volume Pricing	Contact Us

6.00	9.00	7.95	VIS-NIR (400-1000nm)	N-SF5	#45-466	£36.77 Volume Pricing	20+ In Stock
6.00	10.00	8.82	VIS-NIR (400-1000nm)	N-BK7	#38-483	£36.77 Volume Pricing	10 In Stock
6.00	12.00	10.94	VIS-NIR (400-1000nm)	N-BK7	#45-467	£35.90 Volume Pricing	20+ In Stock
6.00	15.00	13.68	VIS-NIR (400-1000nm)	N-BK7	#45-468	£35.90 Volume Pricing	20+ In Stock
6.00	18.00	17.07	VIS-NIR (400-1000nm)	N-BK7	#45-469	£35.90 Volume Pricing	8 In Stock
6.00	20.00	19.04	VIS-NIR (400-1000nm)	N-BK7	#38-484	£35.90 Volume Pricing	5 In Stock
6.00	21.00	20.06	VIS-NIR (400-1000nm)	N-BK7	#45-470	£35.90 Volume Pricing	20+ In Stock
6.00	24.00	23.01	VIS-NIR (400-1000nm)	N-BK7	#45-471	£35.90 Volume Pricing	20+ In Stock
6.00	25.00	24.04	VIS-NIR (400-1000nm)	N-BK7	#38-485	£35.90 Volume Pricing	4 In Stock
6.00	30.00	29.14	VIS-NIR (400-1000nm)	N-BK7	#45-472	£35.90 Volume Pricing	9 In Stock
6.00	36.00	34.95	VIS-NIR (400-1000nm)	N-BK7	#45-473	£35.90 Volume Pricing	2 In Stock
6.00	48.00	46.95	VIS-NIR (400-1000nm)	N-BK7	#47-381	£35.90 Volume Pricing	1 In Stock
6.00	60.00	58.95	VIS-NIR (400-1000nm)	N-BK7	#67-178	£35.90 Volume Pricing	7 In Stock
6.00	72.00	70.97	VIS-NIR (400-1000nm)	N-BK7	#45-696	£35.90 Volume Pricing	6 In Stock

7.00	7.00	5.50	VIS-NIR (400-1000nm)	N-SF11	#71-298	£36.77 Volume Pricing	Contact Us
7.00	10.00	8.10	VIS-NIR (400-1000nm)	N-BK7	#71-305	£36.33 Volume Pricing	6 In Stock
7.00	12.00	10.30	VIS-NIR (400-1000nm)	N-BK7	#71-312	£36.33 Volume Pricing	5 In Stock
8.00	8.00	6.40	VIS-NIR (400-1000nm)	N-SF11	#71-319	£36.77 Volume Pricing	Contact Us
8.00	10.00	7.60	VIS-NIR (400-1000nm)	N-BK7	#71-326	£36.33 Volume Pricing	5 In Stock
8.00	12.00	10.00	VIS-NIR (400-1000nm)	N-BK7	#71-333	£36.33 Volume Pricing	4 In Stock
9.00	9.00	7.32	VIS-NIR (400-1000nm)	N-SF11	#45-474	£37.65 Volume Pricing	1 In Stock
9.00	10.00	8.49	VIS-NIR (400-1000nm)	N-SF11	#38-486	£37.65 Volume Pricing	Contact Us
9.00	12.00	10.60	VIS-NIR (400-1000nm)	N-SF11	#49-915	£37.65 Volume Pricing	1 In Stock
9.00	13.50	11.94	VIS-NIR (400-1000nm)	N-SF5	#45-475	£37.65 Volume Pricing	20+ In Stock
9.00	15.00	13.02	VIS-NIR (400-1000nm)	N-BK7	#49-916	£37.65 Volume Pricing	20+ In Stock
9.00	18.00	16.41	VIS-NIR (400-1000nm)	N-BK7	#45-476	£36.77 Volume Pricing	20+ In Stock
9.00	20.00	18.55	VIS-NIR (400-1000nm)	N-BK7	#38-487	£36.77 Volume Pricing	16 In Stock
9.00	22.00	20.73	VIS-NIR (400-1000nm)	N-BK7	#45-477	£36.77 Volume Pricing	9 In Stock

9.00	25.00	23.68	VIS-NIR (400-1000nm)	N-BK7	#38-488	£36.77 Volume Pricing	20+ In Stock
9.00	27.00	25.34	VIS-NIR (400-1000nm)	N-BK7	#45-478	£36.77 Volume Pricing	7 In Stock
9.00	36.00	34.48	VIS-NIR (400-1000nm)	N-BK7	#45-479	£36.77 Volume Pricing	20+ In Stock
9.00	45.00	43.98	VIS-NIR (400-1000nm)	N-BK7	#45-703	£36.77 Volume Pricing	1 In Stock
9.00	54.00	52.69	VIS-NIR (400-1000nm)	N-BK7	#67-179	£36.77 Volume Pricing	3 In Stock
9.00	72.00	70.68	VIS-NIR (400-1000nm)	N-BK7	#67-180	£36.77 Volume Pricing	3 In Stock
9.00	90.00	88.68	VIS-NIR (400-1000nm)	N-BK7	#67-181	£36.77 Volume Pricing	1 In Stock
10.00	10.00	8.18	VIS-NIR (400-1000nm)	N-SF11	#63-519	£37.65 Volume Pricing	Contact Us
10.00	15.00	13.32	VIS-NIR (400-1000nm)	N-SF11	#63-520	£37.65 Volume Pricing	20+ In Stock
10.00	20.00	18.03	VIS-NIR (400-1000nm)	N-BK7	#63-521	£36.77 Volume Pricing	20+ In Stock
10.00	25.00	23.02	VIS-NIR (400-1000nm)	N-BK7	#63-522	£36.77 Volume Pricing	9 In Stock
10.00	30.00	28.01	VIS-NIR (400-1000nm)	N-BK7	#63-523	£36.77 Volume Pricing	9 In Stock
10.00	40.00	38.02	VIS-NIR (400-1000nm)	N-BK7	#63-524	£36.77 Volume Pricing	14 In Stock
10.00	50.00	48.02	VIS-NIR (400-1000nm)	N-BK7	#63-525	£36.77 Volume Pricing	2 In Stock

10.00	75.00	73.02	VIS-NIR (400-1000nm)	N-BK7	#63-526	£36.77 Volume Pricing	Contact Us
10.00	100.00	98.02	VIS-NIR (400-1000nm)	N-BK7	#63-527	£36.77 Volume Pricing	20+ In Stock
12.00	12.00	9.76	VIS-NIR (400-1000nm)	N-SF11	#45-480	£40.71 Volume Pricing	20+ In Stock
12.00	15.00	12.03	VIS-NIR (400-1000nm)	N-BK7	#45-481	£40.71 Volume Pricing	20+ In Stock
12.00	18.00	16.22	VIS-NIR (400-1000nm)	N-SF5	#45-482	£40.71 Volume Pricing	20+ In Stock
12.00	20.00	17.69	VIS-NIR (400-1000nm)	N-BK7	#49-917	£40.71 Volume Pricing	4 In Stock
12.00	24.00	22.15	VIS-NIR (400-1000nm)	N-BK7	#45-483	£39.83 Volume Pricing	5 In Stock
12.00	30.00	28.02	VIS-NIR (400-1000nm)	N-BK7	#45-484	£39.83 Volume Pricing	20+ In Stock
12.00	36.00	34.02	VIS-NIR (400-1000nm)	N-BK7	#33-355	£39.83 Volume Pricing	13 In Stock
12.00	42.00	40.22	VIS-NIR (400-1000nm)	N-BK7	#45-485	£39.83 Volume Pricing	20+ In Stock
12.00	48.00	46.36	VIS-NIR (400-1000nm)	N-BK7	#45-486	£39.83 Volume Pricing	Contact Us
12.00	54.00	52.02	VIS-NIR (400-1000nm)	N-BK7	#45-487	£39.83 Volume Pricing	14 In Stock
12.00	60.00	58.37	VIS-NIR (400-1000nm)	N-BK7	#45-488	£39.83 Volume Pricing	20+ In Stock
12.00	72.00	70.42	VIS-NIR (400-1000nm)	N-BK7	#45-705	£39.83 Volume Pricing	4 In Stock

12.00	84.00	82.39	VIS-NIR (400-1000nm)	N-BK7	#45-489	£39.83 Volume Pricing	20+ In Stock
12.00	100.00	98.35	VIS-NIR (400-1000nm)	N-BK7	#45-490	£39.83 Volume Pricing	20+ In Stock
12.50	17.50	15.00	VIS-NIR (400-1000nm)	N-BK7	#38-501	£39.83 Volume Pricing	2 In Stock
12.50	35.00	33.42	VIS-NIR (400-1000nm)	N-BK7	#38-506	£38.95 Volume Pricing	4 In Stock
12.70	12.70	10.46	VIS-NIR (400-1000nm)	N-SF11	#62-591	£39.83 Volume Pricing	20+ In Stock
12.70	15.00	11.53	VIS-NIR (400-1000nm)	N-BK7	#62-592	£39.83 Volume Pricing	8 In Stock
12.70	19.10	16.46	VIS-NIR (400-1000nm)	N-BK7	#62-593	£39.83 Volume Pricing	5 In Stock
12.70	20.00	17.49	VIS-NIR (400-1000nm)	N-BK7	#38-515	£39.83 Volume Pricing	Contact Us
12.70	25.40	23.43	VIS-NIR (400-1000nm)	N-BK7	#62-594	£38.95 Volume Pricing	16 In Stock
12.70	30.00	28.22	VIS-NIR (400-1000nm)	N-BK7	#38-516	£38.95 Volume Pricing	4 In Stock
12.70	31.80	29.81	VIS-NIR (400-1000nm)	N-BK7	#62-595	£38.95 Volume Pricing	20+ In Stock
12.70	38.10	36.12	VIS-NIR (400-1000nm)	N-BK7	#62-596	£38.95 Volume Pricing	20+ In Stock
12.70	40.00	38.48	VIS-NIR (400-1000nm)	N-BK7	#38-517	£38.95 Volume Pricing	12 In Stock
12.70	44.50	42.69	VIS-NIR (400-1000nm)	N-BK7	#62-597	£38.95 Volume Pricing	3 In Stock

12.70	50.80	49.15	VIS-NIR (400-1000nm)	N-BK7	#62-598	£38.95 Volume Pricing	14 In Stock
15.00	15.00	11.71	VIS-NIR (400-1000nm)	N-SF5	#45-491	£40.71 Volume Pricing	20+ In Stock
15.00	18.00	15.61	VIS-NIR (400-1000nm)	N-SF5	#49-918	£40.71 Volume Pricing	20+ In Stock
15.00	20.00	17.74	VIS-NIR (400-1000nm)	N-SF5	#63-528	£40.71 Volume Pricing	5 In Stock
15.00	22.50	20.50	VIS-NIR (400-1000nm)	N-SF5	#45-492	£40.71 Volume Pricing	20+ In Stock
15.00	30.00	27.90	VIS-NIR (400-1000nm)	N-BK7	#45-493	£39.83 Volume Pricing	20+ In Stock
15.00	40.00	38.02	VIS-NIR (400-1000nm)	N-BK7	#45-494	£39.83 Volume Pricing	17 In Stock
15.00	45.00	43.35	VIS-NIR (400-1000nm)	N-BK7	#49-919	£39.83 Volume Pricing	5 In Stock
15.00	60.00	58.65	VIS-NIR (400-1000nm)	N-BK7	#47-382	£39.83 Volume Pricing	20+ In Stock
15.00	75.00	73.79	VIS-NIR (400-1000nm)	N-BK7	#47-383	£39.83 Volume Pricing	20+ In Stock
15.00	100.00	98.02	VIS-NIR (400-1000nm)	N-BK7	#45-706	£39.83 Volume Pricing	20+ In Stock
15.00	200.00	197.89	VIS-NIR (400-1000nm)	N-BK7	#14-380	£39.83 Volume Pricing	2 In Stock
15.00	250.00	248.02	VIS-NIR (400-1000nm)	N-BK7	#14-388	£39.83 Volume Pricing	Contact Us
18.00	18.00	15.20	VIS-NIR (400-1000nm)	N-SF11	#48-426	£42.02 Volume Pricing	20+ In Stock

18.00	22.50	20.26	VIS-NIR (400-1000nm)	N-SF11	#49-920	£41.59 Volume Pricing	20+ In Stock
18.00	27.00	24.73	VIS-NIR (400-1000nm)	N-SF5	#45-495	£41.59 Volume Pricing	20+ In Stock
18.00	36.00	33.65	VIS-NIR (400-1000nm)	N-BK7	#45-496	£40.27 Volume Pricing	20+ In Stock
18.00	54.00	52.02	VIS-NIR (400-1000nm)	N-BK7	#45-497	£40.27 Volume Pricing	3 In Stock
18.00	72.00	70.05	VIS-NIR (400-1000nm)	N-BK7	#45-498	£40.27 Volume Pricing	20+ In Stock
20.00	20.00	17.42	VIS-NIR (400-1000nm)	N-SF11	#45-499	£42.47 Volume Pricing	20+ In Stock
20.00	25.00	22.76	VIS-NIR (400-1000nm)	N-SF11	#49-921	£42.02 Volume Pricing	20+ In Stock
20.00	30.00	27.30	VIS-NIR (400-1000nm)	N-BAF10	#45-707	£42.02 Volume Pricing	20+ In Stock
20.00	35.00	32.04	VIS-NIR (400-1000nm)	N-BK7	#49-922	£42.02 Volume Pricing	Contact Us
20.00	40.00	36.77	VIS-NIR (400-1000nm)	N-BK7	#45-500	£40.71 Volume Pricing	20+ In Stock
20.00	50.00	47.87	VIS-NIR (400-1000nm)	N-BK7	#45-501	£40.71 Volume Pricing	20+ In Stock
20.00	60.00	57.03	VIS-NIR (400-1000nm)	N-BK7	#45-502	£40.71 Volume Pricing	20+ In Stock
20.00	70.00	68.03	VIS-NIR (400-1000nm)	N-BK7	#45-503	£40.71 Volume Pricing	14 In Stock
20.00	80.00	78.45	VIS-NIR (400-1000nm)	N-BK7	#47-385	£40.71 Volume Pricing	14 In Stock

20.00	100.00	97.13	VIS-NIR (400-1000nm)	N-BK7	#45-708	£40.71 Volume Pricing	20+ In Stock
20.00	150.00	148.02	VIS-NIR (400-1000nm)	N-BK7	#47-386	£40.71 Volume Pricing	4 In Stock
25.00	25.00	20.22	VIS-NIR (400-1000nm)	N-SF5	#45-504	£44.65 Volume Pricing	20+ In Stock
25.00	30.00	24.69	VIS-NIR (400-1000nm)	N-BK7	#45-505	£44.65 Volume Pricing	5 In Stock
25.00	35.00	30.42	VIS-NIR (400-1000nm)	N-BK7	#45-506	£44.65 Volume Pricing	15 In Stock
25.00	40.00	36.31	VIS-NIR (400-1000nm)	N-BK7	#45-507	£44.65 Volume Pricing	20+ In Stock
25.00	50.00	46.75	VIS-NIR (400-1000nm)	N-BK7	#45-508	£42.90 Volume Pricing	20+ In Stock
25.00	60.00	56.90	VIS-NIR (400-1000nm)	N-BK7	#45-509	£42.90 Volume Pricing	5 In Stock
25.00	75.00	72.00	VIS-NIR (400-1000nm)	N-BK7	#45-510	£42.90 Volume Pricing	20+ In Stock
25.00	85.00	82.17	VIS-NIR (400-1000nm)	N-BK7	#45-511	£42.90 Volume Pricing	Contact Us
25.00	100.00	97.13	VIS-NIR (400-1000nm)	N-BK7	#45-512	£42.90 Volume Pricing	20+ In Stock
25.00	125.00	122.70	VIS-NIR (400-1000nm)	N-BK7	#45-513	£42.90 Volume Pricing	13 In Stock
25.00	150.00	147.81	VIS-NIR (400-1000nm)	N-BK7	#45-514	£42.90 Volume Pricing	20+ In Stock
25.00	175.00	172.85	VIS-NIR (400-1000nm)	N-BK7	#45-515	£42.90 Volume Pricing	12 In Stock

25.00	200.00	197.89	VIS-NIR (400-1000nm)	N-BK7	#33-361	£42.90 Volume Pricing	20+ In Stock
25.00	250.00	248.02	VIS-NIR (400-1000nm)	N-BK7	#67-182	£42.90 Volume Pricing	Contact Us
25.00	300.00	298.02	VIS-NIR (400-1000nm)	N-BK7	#67-183	£42.90 Volume Pricing	20+ In Stock
25.00	400.00	397.89	VIS-NIR (400-1000nm)	N-BK7	#33-367	£42.90 Volume Pricing	7 In Stock
25.00	500.00	497.89	VIS-NIR (400-1000nm)	N-BK7	#47-387	£42.90 Volume Pricing	7 In Stock
25.00	750.00	747.89	VIS-NIR (400-1000nm)	N-BK7	#47-388	£42.90 Volume Pricing	5 In Stock
25.40	25.40	21.48	VIS-NIR (400-1000nm)	N-SF11	#62-599	£44.65 Volume Pricing	20+ In Stock
25.40	38.10	33.48	VIS-NIR (400-1000nm)	N-BK7	#62-600	£44.65 Volume Pricing	11 In Stock
25.40	50.80	47.50	VIS-NIR (400-1000nm)	N-BK7	#62-601	£42.90 Volume Pricing	5 In Stock
25.40	63.50	60.37	VIS-NIR (400-1000nm)	N-BK7	#62-602	£42.90 Volume Pricing	8 In Stock
25.40	76.20	73.56	VIS-NIR (400-1000nm)	N-BK7	#62-603	£42.90 Volume Pricing	5 In Stock
25.40	88.90	86.26	VIS-NIR (400-1000nm)	N-BK7	#62-604	£42.90 Volume Pricing	9 In Stock
25.40	101.60	98.97	VIS-NIR (400-1000nm)	N-BK7	#62-605	£42.90 Volume Pricing	4 In Stock
30.00	30.00	26.13	VIS-NIR (400-1000nm)	N-SF11	#48-662	£51.65 Volume Pricing	20+ In Stock

30.00	40.00	37.20	VIS-NIR (400-1000nm)	N-SF11	#67-184	£49.90 Volume Pricing	15 In Stock
30.00	50.00	46.17	VIS-NIR (400-1000nm)	N-SF5	#45-709	£49.90 Volume Pricing	20+ In Stock
30.00	60.00	56.03	VIS-NIR (400-1000nm)	N-BK7	#47-389	£48.59 Volume Pricing	20+ In Stock
30.00	75.00	70.95	VIS-NIR (400-1000nm)	N-BK7	#45-710	£48.59 Volume Pricing	2 In Stock
30.00	100.00	96.01	VIS-NIR (400-1000nm)	N-BK7	#45-711	£48.59 Volume Pricing	1 In Stock
30.00	120.00	116.04	VIS-NIR (400-1000nm)	N-BK7	#47-390	£48.59 Volume Pricing	20+ In Stock
40.00	40.00	35.13	VIS-NIR (400-1000nm)	N-SF11	#48-663	£60.84 Volume Pricing	20+ In Stock
40.00	60.00	53.90	VIS-NIR (400-1000nm)	N-BK7	#45-712	£60.84 Volume Pricing	14 In Stock
40.00	80.00	74.73	VIS-NIR (400-1000nm)	N-BK7	#33-385	£59.98 Volume Pricing	8 In Stock
40.00	100.00	95.39	VIS-NIR (400-1000nm)	N-BK7	#33-373	£59.98 Volume Pricing	5 In Stock
40.00	200.00	196.7	VIS-NIR (400-1000nm)	N-BK7	#33-379	£59.98 Volume Pricing	5 In Stock
40.00	300.00	296.70	VIS-NIR (400-1000nm)	N-BK7	#47-391	£59.98 Volume Pricing	2 In Stock
40.00	400.00	396.70	VIS-NIR (400-1000nm)	N-BK7	#47-392	£59.98 Volume Pricing	1 In Stock
50.00	50.00	43.28	VIS-NIR (400-1000nm)	N-SF11	#45-715	£65.22 Volume Pricing	6 In Stock

50.00	75.00	67.75	VIS-NIR (400-1000nm)	N-BK7	#45-716	£63.48 Volume Pricing	8 In Stock
50.00	100.00	93.41	VIS-NIR (400-1000nm)	N-BK7	#45-717	£61.29 Volume Pricing	20+ In Stock
50.00	125.00	118.39	VIS-NIR (400-1000nm)	N-BK7	#47-393	£61.29 Volume Pricing	20+ In Stock
50.00	150.00	144.07	VIS-NIR (400-1000nm)	N-BK7	#45-718	£61.29 Volume Pricing	5 In Stock
50.00	175.00	169.05	VIS-NIR (400-1000nm)	N-BK7	#47-394	£61.29 Volume Pricing	5 In Stock
50.00	200.00	196.66	VIS-NIR (400-1000nm)	N-BK7	#47-395	£61.29 Volume Pricing	Contact Us
50.00	250.00	246.74	VIS-NIR (400-1000nm)	N-BK7	#47-396	£61.29 Volume Pricing	6 In Stock
50.00	500.00	496.70	VIS-NIR (400-1000nm)	N-BK7	#47-397	£61.29 Volume Pricing	1 In Stock
50.80	50.81	44.08	VIS-NIR (400-1000nm)	N-SF11	#71-340	£65.22 Volume Pricing	2 In Stock
50.80	76.20	68.95	VIS-NIR (400-1000nm)	N-BK7	#71-347	£63.48 Volume Pricing	1 In Stock
75.00	75.00	53.49	VIS-NIR (400-1000nm)	N-BK7	#86-911	£126.95 Volume Pricing	2 In Stock
75.00	150.00	142.45	VIS-NIR (400-1000nm)	N-BK7	#86-912	£125.20 Volume Pricing	2 In Stock
75.00	200.00	194.24	VIS-NIR (400-1000nm)	N-BK7	#86-913	£125.20 Volume Pricing	10 In Stock
75.00	250.00	244.73	VIS-NIR (400-1000nm)	N-BK7	#86-914	£125.20 Volume Pricing	6 In Stock

75.00	500.00	494.73	VIS-NIR (400-1000nm)	N-BK7	#86-915	£125.20 Volume Pricing	1 In Stock
10.00	12.50	10.99	VIS-NIR (400-1000nm)	N-SF11	#38-489	£37.65 Volume Pricing	1 In Stock
10.00	17.50	15.66	VIS-NIR (400-1000nm)	N-BK7	#38-492	£36.77 Volume Pricing	3 In Stock
12.00	25.00	23.22	VIS-NIR (400-1000nm)	N-BK7	#38-494	£39.83 Volume Pricing	3 In Stock
12.00	50.00	48.75	VIS-NIR (400-1000nm)	N-BK7	#38-496	£39.83 Volume Pricing	5 In Stock
12.50	12.50	10.40	VIS-NIR (400-1000nm)	N-SF11	#38-499	£39.83 Volume Pricing	2 In Stock
12.50	15.00	13.26	VIS-NIR (400-1000nm)	N-SF11	#38-500	£39.83 Volume Pricing	13 In Stock
12.50	20.00	17.69	VIS-NIR (400-1000nm)	N-BK7	#38-503	£39.83 Volume Pricing	6 In Stock
12.50	25.00	22.96	VIS-NIR (400-1000nm)	N-BK7	#38-504	£38.95 Volume Pricing	Contact Us
12.50	30.00	28.22	VIS-NIR (400-1000nm)	N-BK7	#38-505	£38.95 Volume Pricing	7 In Stock
12.50	40.00	38.55	VIS-NIR (400-1000nm)	N-BK7	#38-507	£38.95 Volume Pricing	5 In Stock
12.50	45.00	43.68	VIS-NIR (400-1000nm)	N-BK7	#38-508	£38.95 Volume Pricing	1 In Stock
12.50	50.00	48.68	VIS-NIR (400-1000nm)	N-BK7	#38-509	£38.95 Volume Pricing	17 In Stock
12.50	75.00	73.88	VIS-NIR (400-1000nm)	N-BK7	#38-510	£38.95 Volume Pricing	1 In Stock

12.50	100.00	98.95	VIS-NIR (400-1000nm)	N-BK7	#38-512	£38.95 Volume Pricing	5 In Stock
12.70	100.00	98.88	VIS-NIR (400-1000nm)	N-BK7	#38-518	£38.95 Volume Pricing	6 In Stock
15.00	25.00	22.50	VIS-NIR (400-1000nm)	N-BK7	#38-519	£39.83 Volume Pricing	3 In Stock
15.00	50.00	48.35	VIS-NIR (400-1000nm)	N-BK7	#38-520	£39.83 Volume Pricing	4 In Stock
18.00	20.00	17.59	VIS-NIR (400-1000nm)	N-SF11	#38-521	£41.59 Volume Pricing	4 In Stock
18.00	25.00	21.51	VIS-NIR (400-1000nm)	N-BK7	#38-522	£41.59 Volume Pricing	1 In Stock
18.00	30.00	27.10	VIS-NIR (400-1000nm)	N-BK7	#38-523	£40.27 Volume Pricing	8 In Stock
18.00	50.00	48.09	VIS-NIR (400-1000nm)	N-BK7	#38-524	£40.27 Volume Pricing	5 In Stock
25.40	35.00	30.46	VIS-NIR (400-1000nm)	N-BK7	#38-525	£44.65 Volume Pricing	2 In Stock
25.40	40.00	36.11	VIS-NIR (400-1000nm)	N-BK7	#38-542	£44.65 Volume Pricing	Contact Us
25.40	75.00	72.69	VIS-NIR (400-1000nm)	N-BK7	#38-543	£42.90 Volume Pricing	3 In Stock
25.40	100.00	98.02	VIS-NIR (400-1000nm)	N-BK7	#38-544	£42.90 Volume Pricing	8 In Stock
25.40	125.00	123.02	VIS-NIR (400-1000nm)	N-BK7	#38-545	£42.90 Volume Pricing	1 In Stock
25.40	150.00	148.02	VIS-NIR (400-1000nm)	N-BK7	#38-547	£42.90 Volume Pricing	1 In Stock

35.00	35.00	30.52	VIS-NIR (400-1000nm)	N-SF11	#38-548	£52.96 Volume Pricing	Contact Us
35.00	50.00	44.40	VIS-NIR (400-1000nm)	N-BK7	#38-552	£51.65 Volume Pricing	2 In Stock
35.00	70.00	66.04	VIS-NIR (400-1000nm)	N-BK7	#38-561	£51.65 Volume Pricing	5 In Stock
35.00	100.00	97.03	VIS-NIR (400-1000nm)	N-BK7	#38-567	£51.65 Volume Pricing	14 In Stock

[#71-870 New](#)



New

Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!

75.00	100.00	87.57	VIS-NIR (400-1000nm)	N-BK7		£125.20 Volume Pricing	4 In Stock
-------	--------	-------	-------------------------	-----------------------	--	---	------------

[#71-871 New](#)



New

Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!

75.00 125.00 115.99

VIS-NIR
(400-1000nm)

[N-BK7](#)

£125.20
[Volume Pricing](#)

7 In Stock

[#71-872 New](#)



New

Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!

75.00 175.00 168.68

VIS-NIR
(400-1000nm)

[N-BK7](#)

£125.20
[Volume Pricing](#)

1 In Stock

[#71-873 New](#)



New

Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!

75.00 300.00 294.4

VIS-NIR
(400-1000nm)

[N-BK7](#)

£125.20
[Volume Pricing](#)

2 In Stock

[#71-874 New](#)



New

Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!

75.00 400.00 394.4

VIS-NIR
(400-1000nm)

[N-BK7](#)

£125.20
[Volume Pricing](#)

4 In Stock

[#71-875 New](#)



New

Launched
on our
website

appearing
in our
latest print
catalogs.

Be the
first to buy
before
anyone
else!



Copyright 2023 | Edmund Optics Ltd Unit 1, Opus Avenue, Poppleton, York, YO26 6BL, UK
Phone: 1-800-363-5992 : (400-[N-BK7](#) £125.20
www.edmundoptics.com 1000nm) [Volume Pricing](#)

1 In Stock