

[All Products](#) / [Optics](#) / [Optical Lenses](#) / [UV Lenses](#)

TECHSPEC® Laser Grade Plano-Convex (PCX) Lenses



- Guaranteed Laser Damage Threshold
- 10-5 Surface Quality
- $\lambda/10$ Surface Accuracy

Common Specifications

Physical & Mechanical Properties




Bevel: Protective as needed

Optical Properties


Substrate: [Fused Silica](#) (Corning 7980)

Power (P-V) @ 632.8nm: λ

Technical Information



1064nm V-Coat
 $R_{(obs)} < 0.25\%$ @ 1064nm



Products

Dia. (mm)	EFL (mm)	BFL (mm)	Coating	Substrate	Stock Number	Price	Buy
6.00	12.00	10.63	Uncoated	Fused Silica	#87-924	£121.69 Volume Pricing	20+ In Stock
6.00	12.00	10.63	Laser V-Coat (266nm)	Fused Silica	#87-928	£149.71 Volume Pricing	11 In Stock
6.00	12.00	10.63	Laser V-Coat (355nm)	Fused Silica	#87-932	£149.71 Volume Pricing	7 In Stock
6.00	12.00	10.63	Laser V-Coat (532nm)	Fused Silica	#87-936	£149.71 Volume Pricing	20+ In Stock
6.00	12.00	10.63	Laser V-Coat (1064nm)	Fused Silica	#87-940	£149.71 Volume Pricing	20+ In Stock
6.00	18.00	16.62	Uncoated	Fused Silica	#87-925	£121.69 Volume Pricing	20+ In Stock
6.00	18.00	16.62	Laser V-Coat (266nm)	Fused Silica	#87-929	£149.71 Volume Pricing	11 In Stock
6.00	18.00	16.62	Laser V-Coat (355nm)	Fused Silica	#87-933	£149.71 Volume Pricing	13 In Stock
6.00	18.00	16.62	Laser V-Coat (532nm)	Fused Silica	#87-937	£149.71 Volume Pricing	13 In Stock
6.00	18.00	16.62	Laser V-Coat (1064nm)	Fused Silica	#87-941	£149.71 Volume Pricing	5 In Stock
6.00	24.00	22.63	Uncoated	Fused Silica	#87-926	£121.69 Volume Pricing	20+ In Stock
6.00	24.00	22.63	Laser V-Coat (266nm)	Fused Silica	#87-930	£149.71 Volume Pricing	14 In Stock
6.00	24.00	22.63	Laser V-Coat (355nm)	Fused Silica	#87-934	£149.71 Volume Pricing	13 In Stock

6.00	24.00	22.63	Laser V-Coat (532nm)	Fused Silica	#87-938	£149.71 Volume Pricing	12 In Stock
6.00	24.00	22.63	Laser V-Coat (1064nm)	Fused Silica	#87-942	£149.71 Volume Pricing	5 In Stock
12.00	18.00	15.23	Uncoated	Fused Silica	#67-090	£130.45 Volume Pricing	5 In Stock
12.00	18.00	15.23	Laser V-Coat (266nm)	Fused Silica	#67-939	£164.59 Volume Pricing	6 In Stock
12.00	18.00	15.23	Laser V-Coat (355nm)	Fused Silica	#67-949	£164.59 Volume Pricing	7 In Stock
12.00	18.00	15.23	Laser V-Coat (532nm)	Fused Silica	#67-959	£164.59 Volume Pricing	7 In Stock
12.00	18.00	15.23	Laser V-Coat (1064nm)	Fused Silica	#67-969	£164.59 Volume Pricing	20+ In Stock
12.00	25.00	22.31	Uncoated	Fused Silica	#67-091	£130.45 Volume Pricing	20+ In Stock
12.00	25.00	22.31	Laser V-Coat (266nm)	Fused Silica	#67-940	£164.59 Volume Pricing	3 In Stock
12.00	25.00	22.31	Laser V-Coat (355nm)	Fused Silica	#67-950	£164.59 Volume Pricing	4 In Stock
12.00	25.00	22.31	Laser V-Coat (532nm)	Fused Silica	#67-960	£164.59 Volume Pricing	Contact Us
12.00	25.00	22.31	Laser V-Coat (1064nm)	Fused Silica	#67-970	£164.59 Volume Pricing	8 In Stock
12.00	36.00	34.29	Uncoated	Fused Silica	#67-092	£130.45 Volume Pricing	20+ In Stock
12.00	36.00	34.29	Laser V-Coat (266nm)	Fused Silica	#67-941	£164.59 Volume Pricing	8 In Stock
12.00	36.00	34.29	Laser V-Coat (355nm)	Fused Silica	#67-951	£164.59 Volume Pricing	1 In Stock

12.00	36.00	34.29	Laser V-Coat (532nm)	Fused Silica	#67-961	£164.59 Volume Pricing	3 In Stock
12.00	36.00	34.29	Laser V-Coat (1064nm)	Fused Silica	#67-971	£164.59 Volume Pricing	1 In Stock
12.00	50.00	48.01	Uncoated	Fused Silica	#67-093	£130.45 Volume Pricing	20+ In Stock
12.00	50.00	48.01	Laser V-Coat (266nm)	Fused Silica	#67-942	£164.59 Volume Pricing	9 In Stock
12.00	50.00	48.01	Laser V-Coat (355nm)	Fused Silica	#67-952	£164.59 Volume Pricing	3 In Stock
12.00	50.00	48.01	Laser V-Coat (532nm)	Fused Silica	#67-962	£164.59 Volume Pricing	8 In Stock
12.00	50.00	48.01	Laser V-Coat (1064nm)	Fused Silica	#67-972	£164.59 Volume Pricing	2 In Stock
12.70	25.00	21.62	Uncoated	Fused Silica	#38-634	£130.45 Volume Pricing	6 In Stock
12.70	25.00	21.62	Laser V-Coat (266nm)	Fused Silica	#38-656	£164.59 Volume Pricing	6 In Stock
12.70	25.00	21.62	Laser V-Coat (355nm)	Fused Silica	#38-681	£164.59 Volume Pricing	Contact Us
12.70	25.00	21.62	Laser V-Coat (532nm)	Fused Silica	#38-707	£164.59 Volume Pricing	3 In Stock
12.70	25.00	21.62	Laser V-Coat (1064nm)	Fused Silica	#38-733	£164.59 Volume Pricing	6 In Stock
12.70	35.00	32.30	Uncoated	Fused Silica	#38-635	£130.45 Volume Pricing	4 In Stock
12.70	35.00	32.30	Laser V-Coat (266nm)	Fused Silica	#38-658	£164.59 Volume Pricing	7 In Stock
12.70	35.00	32.30	Laser V-Coat (355nm)	Fused Silica	#38-684	£164.59 Volume Pricing	5 In Stock

12.70	35.00	32.30	Laser V-Coat (532nm)	Fused Silica	#38-708	£164.59 Volume Pricing	13 In Stock
12.70	35.00	32.30	Laser V-Coat (1064nm)	Fused Silica	#38-734	£164.59 Volume Pricing	2 In Stock
12.70	50.00	47.30	Uncoated	Fused Silica	#38-636	£130.45 Volume Pricing	14 In Stock
12.70	50.00	47.30	Laser V-Coat (266nm)	Fused Silica	#38-660	£164.59 Volume Pricing	5 In Stock
12.70	50.00	47.30	Laser V-Coat (355nm)	Fused Silica	#38-685	£164.59 Volume Pricing	3 In Stock
12.70	50.00	47.30	Laser V-Coat (532nm)	Fused Silica	#38-709	£164.59 Volume Pricing	20+ In Stock
12.70	50.00	47.30	Laser V-Coat (1064nm)	Fused Silica	#38-735	£164.59 Volume Pricing	2 In Stock
12.70	75.00	72.31	Uncoated	Fused Silica	#38-637	£130.45 Volume Pricing	20+ In Stock
12.70	75.00	72.31	Laser V-Coat (266nm)	Fused Silica	#38-661	£164.59 Volume Pricing	4 In Stock
12.70	75.00	72.31	Laser V-Coat (355nm)	Fused Silica	#38-686	£164.59 Volume Pricing	4 In Stock
12.70	75.00	72.31	Laser V-Coat (532nm)	Fused Silica	#38-711	£164.59 Volume Pricing	2 In Stock
12.70	75.00	72.31	Laser V-Coat (1064nm)	Fused Silica	#38-736	£164.59 Volume Pricing	16 In Stock
12.70	100.00	97.32	Uncoated	Fused Silica	#38-638	£130.45 Volume Pricing	6 In Stock
12.70	100.00	97.32	Laser V-Coat (266nm)	Fused Silica	#38-662	£164.59 Volume Pricing	3 In Stock
12.70	100.00	97.32	Laser V-Coat (355nm)	Fused Silica	#38-687	£164.59 Volume Pricing	6 In Stock

12.70	100.00	97.32	Laser V-Coat (532nm)	Fused Silica	#38-712	£164.59 Volume Pricing	5 In Stock
12.70	100.00	97.32	Laser V-Coat (1064nm)	Fused Silica	#38-737	£164.59 Volume Pricing	5 In Stock
12.70	150.00	147.33	Uncoated	Fused Silica	#38-639	£130.45 Volume Pricing	20+ In Stock
12.70	150.00	147.33	Laser V-Coat (266nm)	Fused Silica	#38-665	£164.59 Volume Pricing	7 In Stock
12.70	150.00	147.33	Laser V-Coat (355nm)	Fused Silica	#38-688	£164.59 Volume Pricing	17 In Stock
12.70	150.00	147.33	Laser V-Coat (532nm)	Fused Silica	#38-715	£164.59 Volume Pricing	5 In Stock
12.70	150.00	147.33	Laser V-Coat (1064nm)	Fused Silica	#38-738	£164.59 Volume Pricing	20+ In Stock
12.70	200.00	197.35	Uncoated	Fused Silica	#38-640	£130.45 Volume Pricing	20+ In Stock
12.70	200.00	197.35	Laser V-Coat (266nm)	Fused Silica	#38-666	£164.59 Volume Pricing	4 In Stock
12.70	200.00	197.35	Laser V-Coat (355nm)	Fused Silica	#38-689	£164.59 Volume Pricing	6 In Stock
12.70	200.00	197.35	Laser V-Coat (532nm)	Fused Silica	#38-716	£164.59 Volume Pricing	5 In Stock
12.70	200.00	197.35	Laser V-Coat (1064nm)	Fused Silica	#38-739	£164.59 Volume Pricing	11 In Stock
12.70	250.00	247.36	Uncoated	Fused Silica	#38-641	£130.45 Volume Pricing	20+ In Stock
12.70	250.00	247.36	Laser V-Coat (266nm)	Fused Silica	#38-667	£164.59 Volume Pricing	3 In Stock
12.70	250.00	247.36	Laser V-Coat (355nm)	Fused Silica	#38-690	£164.59 Volume Pricing	5 In Stock

12.70	250.00	247.36	Laser V-Coat (532nm)	Fused Silica	#38-717	£164.59 Volume Pricing	5 In Stock
12.70	250.00	247.36	Laser V-Coat (1064nm)	Fused Silica	#38-740	£164.59 Volume Pricing	6 In Stock
12.70	300.00	297.38	Uncoated	Fused Silica	#38-643	£130.45 Volume Pricing	20+ In Stock
12.70	300.00	297.38	Laser V-Coat (266nm)	Fused Silica	#38-668	£164.59 Volume Pricing	3 In Stock
12.70	300.00	297.38	Laser V-Coat (355nm)	Fused Silica	#38-691	£164.59 Volume Pricing	7 In Stock
12.70	300.00	297.38	Laser V-Coat (532nm)	Fused Silica	#38-718	£164.59 Volume Pricing	4 In Stock
12.70	300.00	297.38	Laser V-Coat (1064nm)	Fused Silica	#38-741	£164.59 Volume Pricing	1 In Stock
12.70	500.00	497.44	Uncoated	Fused Silica	#38-644	£130.45 Volume Pricing	20+ In Stock
12.70	500.00	497.44	Laser V-Coat (266nm)	Fused Silica	#38-669	£164.59 Volume Pricing	3 In Stock
12.70	500.00	497.44	Laser V-Coat (355nm)	Fused Silica	#38-692	£164.59 Volume Pricing	9 In Stock
12.70	500.00	497.44	Laser V-Coat (532nm)	Fused Silica	#38-719	£164.59 Volume Pricing	14 In Stock
12.70	500.00	497.44	Laser V-Coat (1064nm)	Fused Silica	#38-742	£164.59 Volume Pricing	3 In Stock
12.70	1,000.00	997.59	Uncoated	Fused Silica	#38-645	£130.45 Volume Pricing	20+ In Stock
12.70	1,000.00	997.59	Laser V-Coat (266nm)	Fused Silica	#38-670	£164.59 Volume Pricing	1 In Stock
12.70	1,000.00	997.59	Laser V-Coat (355nm)	Fused Silica	#38-693	£164.59 Volume Pricing	3 In Stock

12.70	1,000.00	997.59	Laser V-Coat (532nm)	Fused Silica	#38-720	£164.59 Volume Pricing	8 In Stock
12.70	1,000.00	997.59	Laser V-Coat (1064nm)	Fused Silica	#38-743	£164.59 Volume Pricing	5 In Stock
25.00	38.00	33.03	Uncoated	Fused Silica	#67-094	£162.84 Volume Pricing	20+ In Stock
25.00	38.00	33.03	Laser V-Coat (266nm)	Fused Silica	#67-943	£182.98 Volume Pricing	17 In Stock
25.00	38.00	33.03	Laser V-Coat (355nm)	Fused Silica	#67-953	£182.98 Volume Pricing	8 In Stock
25.00	38.00	33.03	Laser V-Coat (532nm)	Fused Silica	#67-963	£182.98 Volume Pricing	5 In Stock
25.00	38.00	33.03	Laser V-Coat (1064nm)	Fused Silica	#67-973	£182.98 Volume Pricing	2 In Stock
25.00	50.00	46.00	Uncoated	Fused Silica	#67-095	£162.84 Volume Pricing	7 In Stock
25.00	50.00	46.00	Laser V-Coat (266nm)	Fused Silica	#67-944	£182.98 Volume Pricing	7 In Stock
25.00	50.00	46.00	Laser V-Coat (355nm)	Fused Silica	#67-954	£182.98 Volume Pricing	5 In Stock
25.00	50.00	46.00	Laser V-Coat (532nm)	Fused Silica	#67-964	£182.98 Volume Pricing	9 In Stock
25.00	50.00	46.00	Laser V-Coat (1064nm)	Fused Silica	#67-974	£182.98 Volume Pricing	6 In Stock
25.00	75.00	71.96	Uncoated	Fused Silica	#67-096	£162.84 Volume Pricing	13 In Stock
25.00	75.00	71.96	Laser V-Coat (266nm)	Fused Silica	#67-945	£182.98 Volume Pricing	Contact Us
25.00	75.00	71.96	Laser V-Coat (355nm)	Fused Silica	#67-955	£182.98 Volume Pricing	5 In Stock

25.00	75.00	71.96	Laser V-Coat (532nm)	Fused Silica	#67-965	£182.98 Volume Pricing	20+ In Stock
25.00	75.00	71.96	Laser V-Coat (1064nm)	Fused Silica	#67-975	£182.98 Volume Pricing	7 In Stock
25.00	100.00	97.40	Uncoated	Fused Silica	#67-097	£162.84 Volume Pricing	2 In Stock
25.00	100.00	97.4	Laser V-Coat (266nm)	Fused Silica	#67-946	£182.98 Volume Pricing	17 In Stock
25.00	100.00	97.40	Laser V-Coat (355nm)	Fused Silica	#67-956	£182.98 Volume Pricing	5 In Stock
25.00	100.00	97.40	Laser V-Coat (532nm)	Fused Silica	#67-966	£182.98 Volume Pricing	10 In Stock
25.00	100.00	97.40	Laser V-Coat (1064nm)	Fused Silica	#67-976	£182.98 Volume Pricing	9 In Stock
25.00	150.00	147.82	Uncoated	Fused Silica	#67-098	£162.84 Volume Pricing	3 In Stock
25.00	150.00	147.86	Laser V-Coat (266nm)	Fused Silica	#67-947	£182.98 Volume Pricing	3 In Stock
25.00	150.00	147.82	Laser V-Coat (355nm)	Fused Silica	#67-957	£182.98 Volume Pricing	20+ In Stock
25.00	150.00	147.82	Laser V-Coat (532nm)	Fused Silica	#67-967	£182.98 Volume Pricing	Contact Us
25.00	150.00	147.82	Laser V-Coat (1064nm)	Fused Silica	#67-977	£182.98 Volume Pricing	Contact Us
25.00	250.00	248.14	Uncoated	Fused Silica	#67-099	£162.84 Volume Pricing	1 In Stock
25.00	250.00	248.14	Laser V-Coat (266nm)	Fused Silica	#67-948	£182.98 Volume Pricing	15 In Stock
25.00	250.00	248.14	Laser V-Coat (355nm)	Fused Silica	#67-958	£182.98 Volume Pricing	6 In Stock

25.00	250.00	248.14	Laser V-Coat (532nm)	Fused Silica	#67-968	£182.98 Volume Pricing	5 In Stock
25.00	250.00	248.14	Laser V-Coat (1064nm)	Fused Silica	#67-978	£182.98 Volume Pricing	6 In Stock
25.40	35.00	28.55	Uncoated	Fused Silica	#38-624	£162.84 Volume Pricing	9 In Stock
25.40	35.00	28.55	Laser V-Coat (266nm)	Fused Silica	#38-646	£182.98 Volume Pricing	7 In Stock
25.40	35.00	28.55	Laser V-Coat (355nm)	Fused Silica	#38-671	£182.98 Volume Pricing	16 In Stock
25.40	35.00	28.55	Laser V-Coat (532nm)	Fused Silica	#38-694	£182.98 Volume Pricing	1 In Stock
25.40	35.00	28.55	Laser V-Coat (1064nm)	Fused Silica	#38-721	£182.98 Volume Pricing	2 In Stock
25.40	50.00	45.71	Uncoated	Fused Silica	#38-625	£162.84 Volume Pricing	3 In Stock
25.40	50.00	45.71	Laser V-Coat (266nm)	Fused Silica	#38-647	£182.98 Volume Pricing	3 In Stock
25.40	50.00	45.71	Laser V-Coat (355nm)	Fused Silica	#38-672	£182.98 Volume Pricing	5 In Stock
25.40	50.00	45.71	Laser V-Coat (532nm)	Fused Silica	#38-695	£182.98 Volume Pricing	7 In Stock
25.40	50.00	45.71	Laser V-Coat (1064nm)	Fused Silica	#38-722	£182.98 Volume Pricing	3 In Stock
25.40	75.00	71.63	Uncoated	Fused Silica	#38-626	£162.84 Volume Pricing	6 In Stock
25.40	75.00	71.63	Laser V-Coat (266nm)	Fused Silica	#38-648	£182.98 Volume Pricing	5 In Stock
25.40	75.00	71.63	Laser V-Coat (355nm)	Fused Silica	#38-673	£182.98 Volume Pricing	4 In Stock

25.40	75.00	71.63	Laser V-Coat (532nm)	Fused Silica	#38-699	£182.98 Volume Pricing	4 In Stock
25.40	75.00	71.63	Laser V-Coat (1064nm)	Fused Silica	#38-723	£182.98 Volume Pricing	2 In Stock
25.40	100.00	97.32	Uncoated	Fused Silica	#38-627	£162.84 Volume Pricing	Contact Us
25.40	100.00	97.32	Laser V-Coat (266nm)	Fused Silica	#38-649	£182.98 Volume Pricing	Contact Us
25.40	100.00	97.32	Laser V-Coat (355nm)	Fused Silica	#38-674	£182.98 Volume Pricing	10 In Stock
25.40	100.00	97.32	Laser V-Coat (532nm)	Fused Silica	#38-700	£182.98 Volume Pricing	3 In Stock
25.40	100.00	97.32	Laser V-Coat (1064nm)	Fused Silica	#38-724	£182.98 Volume Pricing	14 In Stock
25.40	150.00	147.33	Uncoated	Fused Silica	#38-628	£162.84 Volume Pricing	16 In Stock
25.40	150.00	147.33	Laser V-Coat (266nm)	Fused Silica	#38-650	£182.98 Volume Pricing	3 In Stock
25.40	150.00	147.33	Laser V-Coat (355nm)	Fused Silica	#38-675	£182.98 Volume Pricing	12 In Stock
25.40	150.00	147.33	Laser V-Coat (532nm)	Fused Silica	#38-701	£182.98 Volume Pricing	3 In Stock
25.40	150.00	147.33	Laser V-Coat (1064nm)	Fused Silica	#38-725	£182.98 Volume Pricing	7 In Stock
25.40	200.00	197.35	Uncoated	Fused Silica	#38-629	£162.84 Volume Pricing	8 In Stock
25.40	200.00	197.35	Laser V-Coat (266nm)	Fused Silica	#38-651	£182.98 Volume Pricing	4 In Stock
25.40	200.00	197.35	Laser V-Coat (355nm)	Fused Silica	#38-676	£182.98 Volume Pricing	9 In Stock

25.40	200.00	197.35	Laser V-Coat (532nm)	Fused Silica	#38-702	£182.98 Volume Pricing	10 In Stock
25.40	200.00	197.35	Laser V-Coat (1064nm)	Fused Silica	#38-726	£182.98 Volume Pricing	Contact Us
25.40	250.00	247.36	Uncoated	Fused Silica	#38-630	£162.84 Volume Pricing	20+ In Stock
25.40	250.00	247.36	Laser V-Coat (266nm)	Fused Silica	#38-652	£182.98 Volume Pricing	4 In Stock
25.40	250.00	247.36	Laser V-Coat (355nm)	Fused Silica	#38-677	£182.98 Volume Pricing	7 In Stock
25.40	250.00	247.36	Laser V-Coat (532nm)	Fused Silica	#38-703	£182.98 Volume Pricing	9 In Stock
25.40	250.00	247.36	Laser V-Coat (1064nm)	Fused Silica	#38-727	£182.98 Volume Pricing	2 In Stock
25.40	300.00	297.38	Uncoated	Fused Silica	#38-631	£162.84 Volume Pricing	20+ In Stock
25.40	300.00	297.38	Laser V-Coat (266nm)	Fused Silica	#38-653	£182.98 Volume Pricing	5 In Stock
25.40	300.00	297.38	Laser V-Coat (355nm)	Fused Silica	#38-678	£182.98 Volume Pricing	4 In Stock
25.40	300.00	297.38	Laser V-Coat (532nm)	Fused Silica	#38-704	£182.98 Volume Pricing	5 In Stock
25.40	300.00	297.38	Laser V-Coat (1064nm)	Fused Silica	#38-729	£182.98 Volume Pricing	5 In Stock
25.40	500.00	497.44	Uncoated	Fused Silica	#38-632	£162.84 Volume Pricing	9 In Stock
25.40	500.00	497.44	Laser V-Coat (266nm)	Fused Silica	#38-654	£182.98 Volume Pricing	6 In Stock
25.40	500.00	497.44	Laser V-Coat (355nm)	Fused Silica	#38-679	£182.98 Volume Pricing	Contact Us

25.40	500.00	497.44	Laser V-Coat (532nm)	Fused Silica	#38-705	£182.98 Volume Pricing	3 In Stock
25.40	500.00	497.44	Laser V-Coat (1064nm)	Fused Silica	#38-731	£182.98 Volume Pricing	6 In Stock
25.40	1,000.00	997.59	Uncoated	Fused Silica	#38-633	£162.84 Volume Pricing	20+ In Stock
25.40	1,000.00	997.59	Laser V-Coat (266nm)	Fused Silica	#38-655	£182.98 Volume Pricing	4 In Stock
25.40	1,000.00	997.59	Laser V-Coat (355nm)	Fused Silica	#38-680	£182.98 Volume Pricing	3 In Stock
25.40	1,000.00	997.59	Laser V-Coat (532nm)	Fused Silica	#38-706	£182.98 Volume Pricing	13 In Stock
25.40	1,000.00	997.59	Laser V-Coat (1064nm)	Fused Silica	#38-732	£182.98 Volume Pricing	7 In Stock

[#70-003 New](#)



New

Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!

50.80	100.00	91.773	Uncoated	Fused Silica		£328.31 Volume Pricing	20+ In Stock
-------	--------	--------	----------	------------------------------	--	---	--------------

[#70-004 New](#)



New

Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!

50.80 150.00 143.144 Uncoated

[Fused Silica](#)

£328.31
[Volume Pricing](#)

20+ In Stock

[#70-005 New](#)



New

Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!

50.80 200.00 194.515 Uncoated

[Fused Silica](#)

£328.31
[Volume Pricing](#)

6 In Stock

[#70-006 New](#)



New

Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!

50.80 250.00 244.514 Uncoated

[Fused Silica](#)

£328.31
[Volume Pricing](#)

20+ In Stock

[#70-007 New](#)



New

Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!

50.80 300.00 294.516 Uncoated

[Fused Silica](#)

£328.31
[Volume Pricing](#)

15 In Stock

[#70-013 New](#)



New

Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!

£346.70
[Volume Pricing](#)

4 In Stock

50.80 100.00 91.773 Laser V-Coat (266nm) [Fused Silica](#)

[#70-014 New](#)



New

Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!

£346.70
[Volume Pricing](#)

4 In Stock

50.80 150.00 143.144 Laser V-Coat (266nm) [Fused Silica](#)

[#70-016 New](#)



New

Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!

50.80 250.00 244.514

Laser V-Coat (266nm)

[Fused Silica](#)

£346.70
[Volume Pricing](#)

5 In Stock

[#70-017 New](#)



New

Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!

50.80 300.00 294.516

Laser V-Coat (266nm)

[Fused Silica](#)

£346.70
[Volume Pricing](#)

9 In Stock

[#70-023 New](#)



New

Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!

50.80 100.00 91.773

Laser V-Coat (355nm)

[Fused Silica](#)

£346.70
[Volume Pricing](#)

5 In Stock

[#70-024 New](#)



New

Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!

50.80 150.00 143.144

Laser V-Coat (355nm)

[Fused Silica](#)

£346.70
[Volume Pricing](#)

5 In Stock

[#70-025 New](#)



New

Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!

50.80 200.00 194.515

Laser V-Coat (355nm)

[Fused Silica](#)

£346.70
[Volume Pricing](#)

5 In Stock

[#70-026 New](#)



New

Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!

50.80 250.00 244.514

Laser V-Coat (355nm)

[Fused Silica](#)

£346.70
[Volume Pricing](#)

5 In Stock

[#70-027 New](#)



New

Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!

50.80 300.00 294.516

Laser V-Coat
(355nm)

[Fused Silica](#)

£346.70
[Volume Pricing](#)

5 In Stock

[#70-033 New](#)



New

Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!

50.80 100.00 91.773

Laser V-Coat
(532nm)

[Fused Silica](#)

£346.70
[Volume Pricing](#)

2 In Stock

[#70-034 New](#)



New

Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!

50.80 150.00 143.144

Laser V-Coat (532nm)

[Fused Silica](#)

£346.70
[Volume Pricing](#)

1 In Stock

[#70-035 New](#)



New

Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!

50.80 200.00 194.515

Laser V-Coat (532nm)

[Fused Silica](#)

£346.70
[Volume Pricing](#)

13 In Stock

[#70-036 New](#)



New

Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!

50.80 250.00 244.514

Laser V-Coat (532nm)

[Fused Silica](#)

£346.70
[Volume Pricing](#)

1 In Stock

[#70-037 New](#)



New

Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!

50.80 300.00 294.516

Laser V-Coat (532nm)

[Fused Silica](#)

£346.70
[Volume Pricing](#)

7 In Stock

[#70-043 New](#)



New

Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!

50.80 100.00 91.773

Laser V-Coat
(1064nm)

[Fused Silica](#)

£346.70
[Volume Pricing](#)

2 In Stock

[#70-044 New](#)



New

Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!

50.80 150.00 143.144

Laser V-Coat
(1064nm)

[Fused Silica](#)

£346.70
[Volume Pricing](#)

7 In Stock

[#70-045 New](#)



New

Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!

£346.70
[Volume Pricing](#)

4 In Stock

50.80 200.00 194.515 Laser V-Coat (1064nm) [Fused Silica](#)

[#70-046 New](#)



New

Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!

£346.70
[Volume Pricing](#)

5 In Stock

50.80 200.00 194.515 Laser V-Coat (1064nm) [Fused Silica](#)



Edmund
optics | worldwide

Copyright 2023 | Edmund Optics, Ltd Unit 1, Opus Avenue, Nether Poppleton, York, YO26 6BL, UK
Phone: 1-800-363-1992 : www.edmundoptics.com