880nm CWL, 50nm FWHM, 25mm Mounted Diameter

Stock **#65-748** 3-4 DAYS

Additional Bandwidths

- 1 + **£140.25**

ADD TO CART

Qty 1-9
£140.25

Qty 10+
£126.06

Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

CUSTOM OPTIONS

Diameter (mm): 25.00 +0.0/-0.2
Angle of Incidence (°): 0
Optical Density OD (Average):

≥3.0

Clear Aperture CA (mm):
21.0

Center Wavelength CWL (nm):
880.00 ±15

Center Wavelength CWL Tolerance (nm):
±15

Full Width-Half Max FWHM (nm):
50.00 ±15

Full Width-Half Max FWHM Tolerance (nm):
±15

Minimum Transmission (%):
≥55

Operating Temperature (°C):
-50 to +75

Coating:
Traditional Coated

Surface Quality:
80-50

Thickness Tolerance (mm):
±0.1

Type:
Bandpass Filter

Typical Applications:
LED/Laser Cleanup

Blocking Wavelength Range (nm):
200 - 1200

Construction:
Mounted in Black Anodized Ring

Mount Thickness (mm):
7.5 ±0.1

Regulatory Compliance

RoHS 2015:
Compliant

Reach 219:
Compliant

Certificate of Conformance:
View