# 1200 Grooves, 25mm Square, 750nm NIR Ruled Grating



Stock **#43-848** 3-4 DAYS

- 1 + **£136.00**

ADD TO CART

Qty 1+

**£136.00**

Volume Pricing

Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

SPECIAL HANDLING

**Groove Density (grooves/mm):**
1200

**Wavelength Range (nm):**
700 - 3000

**Blaze Wavelength (nm):**
750

**Blaze Angle (°):**
26.73

**Dimensions (mm):**
25.0 x 25.0 ±0.5

**Clear Aperture (%):**
90

**Coating:**
Bare Gold

**Construction:**
Ruled Grating

**Direction of Grooves:**
Parallel to Short Dimension

**Length (mm):**
25.00

**Substrate:**
Float Glass

**Thickness (mm):**
9.50 ±0.5

**Type:**
Reflective Diffraction Grating

**Width (mm):**
25.00

**Alignment of Grooves to Edge (°):**
±0.5

## Regulatory Compliance

**RoHS 2015:**
Compliant

**Reach 219:**
Compliant

**Certificate of Conformance:**
View