

[All Products](#) / [Optics](#) / [Optical Lenses](#) / [Plano-Concave \(PCV\) Lenses](#)

TECHSPEC® UV Fused Silica Plano-Concave (PCV) Lenses



- Negative Focal Lengths for Beam Expansion or Light Projection Applications
- Wavelength Range of 200 - 2200nm
- Popular UV-AR Coating Option Available

Common Specifications

General

Note:

Max. Flat Annulus is 0.3mm

Optical Properties



 Substrate: [Fused Silica](#) (Corning 7980)

Surface Quality: 40-20

Power (P-V) @ 632.8nm: 1.5λ

Irregularity (P-V) @ 632.8nm: λ/4

Technical Information



UV FS Transmission Curve

Products

Dia. (mm)	EFL (mm)	BFL (mm)	Coating	Substrate	Stock Number	Price	Buy
6.00	-9.00	-10.38	Uncoated	Fused Silica	#45-697	£98.06 Volume Pricing	12 In Stock
6.00	-12.00	-13.38	Uncoated	Fused Silica	#45-698	£98.06 Volume Pricing	20+ In Stock
6.00	-18.00	-19.37	Uncoated	Fused Silica	#45-699	£98.06 Volume Pricing	20+ In Stock
6.00	-9.00	-10.38	UV-AR (250-425nm)	Fused Silica	#46-308	£118.19 Volume Pricing	20+ In Stock
6.00	-9.00	-10.38	UV-VIS (250-700nm)	Fused Silica	#71-091	£118.19 Volume Pricing	8 In Stock
6.00	-12.00	-13.38	UV-AR (250-425nm)	Fused Silica	#46-309	£118.19 Volume Pricing	20+ In Stock
6.00	-12.00	-13.38	UV-VIS (250-700nm)	Fused Silica	#71-092	£118.19 Volume Pricing	3 In Stock
6.00	-18.00	-19.37	UV-AR (250-425nm)	Fused Silica	#46-310	£118.19 Volume Pricing	20+ In Stock
6.00	-18.00	-19.37	UV-VIS (250-700nm)	Fused Silica	#71-093	£118.19 Volume Pricing	4 In Stock
6.00	-9.00	-10.38	VIS-NIR (400-1000nm)	Fused Silica	#21-043	£118.19 Volume Pricing	7 In Stock
6.00	-12.00	-13.38	VIS-NIR (400-1000nm)	Fused Silica	#21-044	£118.19 Volume Pricing	2 In Stock
6.00	-18.00	-19.37	VIS-NIR (400-1000nm)	Fused Silica	#21-045	£118.19 Volume Pricing	9 In Stock
9.00	-13.00	-14.89	UV-VIS (250-700nm)	Fused Silica	#71-094	£122.57 Volume Pricing	5 In Stock

9.00	-18.00	-19.37	UV-VIS (250-700nm)	Fused Silica	#71-095	£122.57 Volume Pricing	5 In Stock
9.00	-13.50	-14.89	Uncoated	Fused Silica	#45-700	£102.43 Volume Pricing	20+ In Stock
9.00	-18.00	-19.37	Uncoated	Fused Silica	#45-701	£102.43 Volume Pricing	20+ In Stock
9.00	-27.00	-28.42	Uncoated	Fused Silica	#45-702	£102.43 Volume Pricing	20+ In Stock
9.00	-13.50	-14.89	UV-AR (250-425nm)	Fused Silica	#46-311	£122.57 Volume Pricing	12 In Stock
9.00	-18.00	-19.37	UV-AR (250-425nm)	Fused Silica	#46-312	£122.57 Volume Pricing	20+ In Stock
9.00	-27.00	-28.42	UV-VIS (250-700nm)	Fused Silica	#71-096	£122.57 Volume Pricing	5 In Stock
9.00	-27.00	-28.42	UV-AR (250-425nm)	Fused Silica	#46-313	£122.57 Volume Pricing	8 In Stock
9.00	-13.50	-14.89	VIS-NIR (400-1000nm)	Fused Silica	#21-046	£122.57 Volume Pricing	5 In Stock
9.00	-18.00	-19.37	VIS-NIR (400-1000nm)	Fused Silica	#21-047	£122.57 Volume Pricing	5 In Stock
9.00	-27.00	-28.42	VIS-NIR (400-1000nm)	Fused Silica	#21-048	£122.57 Volume Pricing	8 In Stock
12.00	-25.00	-26.37	Uncoated	Fused Silica	#48-046	£107.69 Volume Pricing	17 In Stock
12.00	-30.00	-31.37	Uncoated	Fused Silica	#48-047	£107.69 Volume Pricing	20+ In Stock
12.00	-40.00	-41.37	Uncoated	Fused Silica	#48-048	£107.69 Volume Pricing	20+ In Stock
12.00	-50.00	-51.37	Uncoated	Fused Silica	#48-049	£107.69 Volume Pricing	20+ In Stock
12.00	-	-	Uncoated	Fused Silica	#85-879	£107.69 Volume Pricing	20+ In Stock

12.00	-25.00	-26.37	UV-AR (250-425nm)	Fused Silica	#48-050	£127.82 Volume Pricing	5 In Stock
12.00	-25.00	-26.37	UV-VIS (250-700nm)	Fused Silica	#71-097	£127.82 Volume Pricing	1 In Stock
12.00	-30.00	-31.37	UV-AR (250-425nm)	Fused Silica	#48-051	£127.82 Volume Pricing	20+ In Stock
12.00	-30.00	-31.37	UV-VIS (250-700nm)	Fused Silica	#71-098	£127.82 Volume Pricing	4 In Stock
12.00	-40.00	-41.37	UV-AR (250-425nm)	Fused Silica	#48-052	£127.82 Volume Pricing	4 In Stock
12.00	-40.00	-41.37	UV-VIS (250-700nm)	Fused Silica	#71-099	£127.82 Volume Pricing	2 In Stock
12.00	-50.00	-51.37	UV-AR (250-425nm)	Fused Silica	#48-053	£127.82 Volume Pricing	2 In Stock
12.00	-50.00	-51.37	UV-VIS (250-700nm)	Fused Silica	#71-100	£127.82 Volume Pricing	8 In Stock
12.00	-	-	UV-AR (250-425nm)	Fused Silica	#88-037	£127.82 Volume Pricing	20+ In Stock
12.00	-	-	UV-VIS (250-700nm)	Fused Silica	#71-101	£127.82 Volume Pricing	1 In Stock
12.00	-25.00	-26.37	VIS-NIR (400-1000nm)	Fused Silica	#21-049	£127.82 Volume Pricing	8 In Stock
12.00	-30.00	-31.37	VIS-NIR (400-1000nm)	Fused Silica	#21-050	£127.82 Volume Pricing	1 In Stock
12.00	-40.00	-41.37	VIS-NIR (400-1000nm)	Fused Silica	#21-051	£127.82 Volume Pricing	17 In Stock
12.00	-50.00	-51.37	VIS-NIR (400-1000nm)	Fused Silica	#21-052	£127.82 Volume Pricing	3 In Stock

12.00	- 100.00	- 101.37	VIS-NIR (400- 1000nm)	Fused Silica	#21-053	£127.82 Volume Pricing	3 In Stock
25.00	-50.00	-51.37	Uncoated	Fused Silica	#48-315	£113.82 Volume Pricing	20+ In Stock
25.00	-75.00	-76.71	Uncoated	Fused Silica	#48-316	£113.82 Volume Pricing	20+ In Stock
25.00	- 100.00	- 101.71	Uncoated	Fused Silica	#48-317	£113.82 Volume Pricing	20+ In Stock
25.00	- 150.00	- 151.71	Uncoated	Fused Silica	#48-318	£113.82 Volume Pricing	20+ In Stock
25.00	- 200.00	- 201.71	Uncoated	Fused Silica	#48-319	£113.82 Volume Pricing	3 In Stock
25.00	- 250.00	- 251.71	Uncoated	Fused Silica	#48-320	£113.82 Volume Pricing	20+ In Stock
25.00	-50.00	-51.37	UV-AR (250- 425nm)	Fused Silica	#48-321	£133.08 Volume Pricing	16 In Stock
25.00	-50.00	-51.37	UV-VIS (250- 700nm)	Fused Silica	#71-102	£133.08 Volume Pricing	3 In Stock
25.00	-75.00	-76.71	UV-AR (250- 425nm)	Fused Silica	#48-322	£133.08 Volume Pricing	6 In Stock
25.00	-75.00	-76.71	UV-VIS (250- 700nm)	Fused Silica	#71-103	£133.08 Volume Pricing	2 In Stock
25.00	- 100.00	- 101.71	UV-AR (250- 425nm)	Fused Silica	#48-323	£133.08 Volume Pricing	Contact Us
25.00	- 100.00	- 101.71	UV-VIS (250- 700nm)	Fused Silica	#71-104	£133.08 Volume Pricing	Contact Us
25.00	- 150.00	- 151.71	UV-AR (250- 425nm)	Fused Silica	#48-324	£133.08 Volume Pricing	8 In Stock
25.00	- 150.00	- 151.71	UV-VIS (250- 700nm)	Fused Silica	#71-105	£133.08 Volume Pricing	Contact Us

25.00	- 200.00	- 201.71	UV-AR (250- 425nm)	Fused Silica	#48-325	£133.08 Volume Pricing	5 In Stock
25.00	- 200.00	- 201.71	UV-VIS (250- 700nm)	Fused Silica	#71-106	£133.08 Volume Pricing	6 In Stock
25.00	- 250.00	- 251.71	UV-AR (250- 425nm)	Fused Silica	#48-326	£133.08 Volume Pricing	5 In Stock
25.00	- 250.00	- 251.71	UV-VIS (250- 700nm)	Fused Silica	#71-107	£133.08 Volume Pricing	4 In Stock
25.00	-50.00	-51.37	VIS-NIR (400- 1000nm)	Fused Silica	#21-054	£133.95 Volume Pricing	Contact Us
25.00	-75.00	-76.71	VIS-NIR (400- 1000nm)	Fused Silica	#21-055	£133.95 Volume Pricing	5 In Stock
25.00	- 100.00	- 101.71	VIS-NIR (400- 1000nm)	Fused Silica	#21-056	£133.95 Volume Pricing	3 In Stock
25.00	- 150.00	- 151.71	VIS-NIR (400- 1000nm)	Fused Silica	#21-057	£133.95 Volume Pricing	8 In Stock
25.00	- 200.00	- 201.71	VIS-NIR (400- 1000nm)	Fused Silica	#21-058	£133.95 Volume Pricing	5 In Stock
25.00	- 250.00	- 251.71	VIS-NIR (400- 1000nm)	Fused Silica	#21-059	£133.95 Volume Pricing	8 In Stock



Copyright 2023 | Edmund Optics, Ltd Unit 1, Opus Avenue, Nether Poppleton, York, YO26 6BL, UK
Phone: 1-800-363-1992 :
www.edmundoptics.com